

Boost CX1 PowerLine  
 Bagless cylinder vacuum cleaners  
 for maximum extraction power in a compact design.



- Powerful cleaning performance thanks to vortex technology
- Always stays on track thanks to TrackDrive
- Retains even the smallest particles – Hygiene AirClean filter
- Versatile applications – universal floorhead
- Extremely convenient height adjustment thanks to a Comfort telescopic tube.

EAN: 4002516384656 / Material number: 11666840 / Old Material Number: 41NRF001GB

|                                       |                         |
|---------------------------------------|-------------------------|
| <b>Construction type</b>              |                         |
| Bagless vacuum cleaner                | •                       |
| Product brand                         | Boost CX1               |
| Motor type                            | PowerLine               |
| Product type                          | SNRFO                   |
| Appliance Colour                      | Lotus white             |
| <b>Cleaning</b>                       |                         |
| Vortex Technology                     | •                       |
| <b>User convenience</b>               |                         |
| Electronic suction power control      | 4-stage rotary selector |
| Ergonomic carrying handle             | •                       |
| Ergonomic handle                      | •                       |
| Suction tube                          | Comfort telescopic tube |
| Park system                           | on one side             |
| <b>Efficiency and sustainability</b>  |                         |
| Nominal power consumption in W        | 890                     |
| <b>Mobility</b>                       |                         |
| TrackDrive                            | •                       |
| Operating radius in m                 | 10                      |
| Cable length in m                     | 6.5                     |
| <b>Filter system</b>                  |                         |
| Exhaust filter                        | Hygiene AirClean filter |
| Dustbag volume in l                   | 1.0                     |
| <b>Technical data</b>                 |                         |
| Max. power                            | 890                     |
| Volume in dB                          | 78.0                    |
| Width in mm                           | 400                     |
| Height in mm                          | 280                     |
| Weight in kg                          | 7.8                     |
| <b>Accessories included</b>           |                         |
| Upholstery nozzle                     | •                       |
| Crevice nozzle                        | •                       |
| Dusting brush with synthetic bristles | •                       |
| SBD 365-3 floorhead                   | •                       |
| Cleaning tool                         | No                      |