

PDR 307 HP [EL] Professional heat-pump dryer, Little Giants For simple and flexible installation without vent ducting.



- Drum volume 130.00 l, load size 7.0 kg
- 50 % less energy consumption than vented dryers*
- Tested for intensive use unparalleled Miele quality
- Language-neutral fascia panel with rotary control M Select
- Precision drying of all standard fabrics – PerfectDry

 $[\]dot{}$ Heat pump dryers consume up to 50 % less energy than an electrically heated vented dryer.



EAN: 4002516413585 / Material number: 11693360 / Old Material Number: 52307171GB

Construction type and version	
Construction type	Front-loader, stackable
Range	Evolution
Front	Lotus white
Fascia color	Stainless steel
Load in kg	7.0
Drum volume in I	130.00
Drying system	Heat pump
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for residential homes and apartments	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in I/hour	2.70
· · · · · ·	0.20
Specific energy consumption in kWh/kg Specific energy consumption for Cottons/Normal drying	0.20
programme with residual moisture at 48 % in kW	0.20
Specific energy consumption for mixed fibre fabrics/Normal	0.17
drying programme with residual moisture a	0.17
Programme duration in min.	67
Programme duration for Cottons/Normal drying programme	67
with residual moisture at 48 % in minutes	
Programme duration for mixed fibre fabrics/Normal drying	57
programme with residual moisture at 40 % in	
Control system	
Control system	M Select
Programmability	programmable
User interface	Residual moisture
	controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
_anguage can be selected easily at any time	•
Standard/target grp programmes	
Basic programmes	•
Standard electrical connection	
Heating type	Heat pump
Electrical connection	220-240V~ 50HZ
Electric heater rating in kW	0.00



PDR 307 HP [EL] Professional heat-pump dryer, Little Giants For simple and flexible installation without vent ducting.



EAN: 4002516413585 / Material number: 11693360 / Old Material Number: 52307171GB

Total connected load in kW	1.44
Fuse rating in A	13
Dimensions and weight of dryer	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	777
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	68.5
Gross weight in kg	74
Maximum floor load in N/m ²	920
Emissions data	020
Emission sound pressure level in the workplace	<70 dB(A) re 20 μPa
Heat dissipation into the room in MJ/h	3.60
Features	0.00
Intelligent drum reversal	•
Axial airflow	
Fluff filter in the door	•
	•
Low-maintenance heat exchanger filter system	•
PerfectDry Oct 11 if a day as the	
SoftLift drum ribs	•
Gentle tumble function	
Condensed water drainage	•
Drying basket (optional)	
Drum lighting	
Machine-independent accessories	•
Efficiency and sustainability	
Energy efficiency class	<u> </u>
Condensation efficiency class	. <u>A</u>
Annual energy consumption in kWh	212
Noise in dB(a) in the Cottons Normal dry standard programme with a full load	67
Duration in minutes in the standard programme	92
How it works	Condenser
Load in kg	7.0
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0.61
Refrigerant global warming potential in kg CO2e	1430
Appliance global warming potential in kg CO2e	872.00
Connection options	
Payment system (optional)	•
Optical interface for service access	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
VOL LINO	



PDR 307 HP [EL] Professional heat-pump dryer, Little Giants For simple and flexible installation without vent ducting.



EAN: 4002516413585 / Material number: 11693360 / Old Material Number: 52307171GB

Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•