

## PDR 514 ROP [G]

Professional vented dryer, gas heating

with M Select ROP residual moisture control for perfect drying results.



- Drum volume 250.00 l, load size 10.0 kg–14.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516408635 / Material number: 11717810 / Old Material Number: 52514009EU

Construction type and version	
Construction type	Front loader
Range	Performance
Front	Iron grey
Fascia color	Stainless steel
Load size with a load ratio of 1:25	10.0
Load size with a load ratio of 1:18	14.0
Drum volume in l	250.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	14.00
Specific energy consumption in kWh/kg	0.55
Programme duration in min.	23
Service life in drying cycles	40000
Control system	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Control panel with easy-to-understand symbols	•
Standard electrical connection	
Heating type	Gas
Electrical connection	1N AC 230V 50HZ
Electric heater rating in kW	0.00
Gas heater rating in kW	15.00
Total connected load in kW	0.60
Fuse rating in A	10

## PDR 514 ROP [G]

Professional vented dryer, gas heating

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516408635 / Material number: 11717810 / Old Material Number: 52514009EU

<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	1400
External dimensions, width in mm	906
External dimensions, depth in mm	852
External dimensions, gross height in mm	1526
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	938
Net weight in kg	162.4
Gross weight in kg	174
Maximum floor load in N/m <sup>2</sup>	1799
<b>Emissions data</b>	
Emission sound pressure level in the workplace	51 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.90
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
DVGW gas	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•