

## PDR 918 [EL] Professional vented dryer, electric heating with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 325.00 I, load size13.0 kg-18.0 kg
- Unique, gentle fabric care honeycomb drum
- Precision drying of all fabrics PerfectDry
- Greatest energy efficiency thanks to Air Recycling
- Connected for the future using LAN and WiFi

EAN: 4002516408697 / Material number: 11717870 / Old Material Number: 52918001EU

| Construction type and venion   |  |
|--|--|
| Construction type and version Construction type                          | Front loader   |
|  | Performance Plus   |
| Range Front  |  |
| Load size with a load ratio of 1:25                                      | Iron grey  |
| Load size with a load ratio of 1:25  Load size with a load ratio of 1:18 | 13.0<br>18.0   |
|  |  |
| Drum volume in I   | 325.00   |
| Drying system  | Exhaust air  |
| Door opening [Ø] in mm   | 520  |
| Door opening angle in degrees  | 180  |
| Door hinge   | _ left   |
| Convertible door hinging   | • Variable of the second of th |
| Stainless steel honeycomb drum   | Yes  |
| Application  |  |
| Suitable for the hotel and catering industry                             |  |
| Suitable for retirement and care homes                                   |  |
| Suitable for facility management   |  |
| Suitable for launderettes  |  |
| Suitable for residential homes and apartments                            |  |
| Suitable for dry cleaners  |  |
| Suitable for commercial laundries  |  |
| Suitable for fire brigades and rescue services                           |  |
| Suitable for studs, riding schools and stables                           |  |
| Suitable for universities, nurseries, and schools                        | •  |
| Suitable for hospitals   | •  |
| Suitable for sports clubs  |  |
| Suitable for beauty salons, spas, and fitness centres                    |  |
| Suitable for doctors' and dentists' practices                            | _ •  |
| Suitable for the petrochemicals industry                                 | •  |
| Suitable for the food-processing industry                                | •  |
| Suitable for amusement parks & holiday complexes                         | •  |
| Suitable for state/community care facilities                             | •  |
| Performance data   |  |
| Maximum evaporation capacity in I/hour                                   | 18.50  |
| Specific energy consumption in kWh/kg                                    | 0.52   |
| Programme duration in min.   | 23   |
| Service life in drying cycles  | 40000  |
| Control system   |  |
| Control system   | M Touch Pro  |
| Programmability  | programmable   |
| User interface   | Residual moisture  |
|  | controlled   |
| Max. delay start in h  | 24   |
| Time left display  | •  |
| Programme sequence indicator   | •  |
| Selectable display languages   | •  |
| Standard electrical connection   |  |
| Heating type   | Electric   |
| Electrical connection  | 3N AC 400V 50/60HZ   |
| Electric heater rating in kW   | 18.00  |
|  |  |



## PDR 918 [EL] Professional vented dryer, electric heating with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516408697 / Material number: 11717870 / Old Material Number: 52918001EU

| Total connected load in kW   | 18.60              |
|--|--------------------|
| Fuse rating in A   | 35                 |
| Dimensions and weight of dryer   |                    |
| External dimensions, height in mm  | 1400               |
| External dimensions, width in mm   | 906                |
| External dimensions, depth in mm   | 1035               |
| External dimensions, gross height in mm                                  | 1526               |
| External dimensions, gross width in mm                                   | 1090               |
| External dimensions, gross depth in mm                                   | 1125               |
| Net weight in kg   | 173.5              |
| Gross weight in kg   | 187                |
| Maximum floor load in N/m <sup>2</sup>                                   | 1967               |
| Emissions data   |                    |
| Emission sound pressure level in the workplace                           | 50 dB(A) re 20 μPa |
| Heat dissipation into the room in MJ/h                                   | 4.50               |
| Features   |                    |
| Intelligent drum reversal  | •                  |
| Axial airflow  | •                  |
| Large-surface fluff filter   | •                  |
| PerfectDry   | •                  |
| SoftLift drum ribs   | •                  |
| AirRecycling Flex  | •                  |
| Communication slot   | •                  |
| Emergency switch-off   | •                  |
| Machine-independent accessories  | •                  |
| Connection options   |                    |
| Payment system (optional)  | •                  |
| Optical interface for service access                                     | •                  |
| Peak load cut-out/energy management (optional)                           | •                  |
| WiFi tumble dryer  | •                  |
| Connector Box  | •                  |
| LAN module (optional)  | •                  |
| Capacities   |                    |
| Respirator masks [number]  | 12                 |
| Overalls [number]  | 2                  |
| Over jackets [number]  | 3                  |
| Synthetic duvets [number]  | 1                  |
| Synthetic pillows [number]   | 3                  |
| Down duvets [number]   | <u>-</u>           |
| Down pillows [number]  | 3                  |
| Cloths, 22 g [number]  | 295                |
| Cotton mops, 40 cm [number]  | 68                 |
| Cotton mops, 50 cm [number]  | 59                 |
| Microfibre mops, 40 cm [number]  | 108                |
| Microfibre mops, 50 cm [number]  | 76                 |
|  | 3                  |
| Summer horse blankets [number]  Standards, test certificates and symbols | 3                  |
| CE   | •                  |
| VDE  | ·                  |
| VDE-EMC  | -                  |
| Splash-proof safety rating IPX4  | •                  |
| Opiaon proof safety rating if 74   | ·                  |



## PDR 918 [EL] Professional vented dryer, electric heating with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516408697 / Material number: 11717870 / Old Material Number: 52918001EU

| WEEE   | • |
|--|---|
| UKCA   | • |
| Complies with Machinery Directive 2006/42/EC | • |