

## PDR 522 ROP [HW]

Professional vented dryer, heated with hot water

with M Select ROP residual moisture control for perfect drying results.



- Unique, gentle fabric care – honeycomb drum
- Drum volume 400.00 l, load size 29 (13.0) lb (kg) – 16.0 kg
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516409113 / Material number: 11718210 / Old Material Number: 52522011EU

Construction type and version	
Construction type	Front loader
Range	Performance
Front	Iron grey
Fascia color	Stainless steel
Load size with a load ratio of 1:32	29 (13.0) lb (kg)
Load size with a load ratio of 1:25	16.0
Drum volume in l	400.00
Drying system	Hot water
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Specific energy consumption in kWh/kg	0.56
Programme duration in min.	60
Service life in drying cycles	40000
Control system	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Control panel with easy-to-understand symbols	•
Standard electrical connection	
Heating type	Hot water
Electrical connection	1N AC 230V 50/60HZ
Electric heater rating in kW	0.00
Heater rating, hot water in kW	9.80
Total connected load in kW	1.00
Fuse rating in A	10
Maximum water intake temperature in °C	90
Dimensions and weight of dryer	
External dimensions, height in mm	1400

## PDR 522 ROP [HW]

Professional vented dryer, heated with hot water

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516409113 / Material number: 11718210 / Old Material Number: 52522011EU

External dimensions, width in mm	906
External dimensions, depth in mm	1162
External dimensions, gross height in mm	1526
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	1254
Net weight in kg	231.9
Gross weight in kg	246
Maximum floor load in N/m <sup>2</sup>	2600
<b>Emissions data</b>	
Emission sound pressure level in the workplace	62 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2.60
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Cloths, 22 g [number]	364
Summer horse blankets [number]	3
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•