

## PDR 528 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



- Drum volume 500.00 l, load size 20.0 kg–28.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516409243 / Material number: 11718340 / Old Material Number: 52528001EU

| Construction type and version                         |                               |
|---|-------------------------------|
| Construction type                                     | Front loader                  |
| Range   | Performance                   |
| Front   | Iron grey                     |
| Fascia color  | Stainless steel               |
| Load size with a load ratio of 1:25                   | 20.0                          |
| Load size with a load ratio of 1:18                   | 28.0                          |
| Drum volume in l                                      | 500.00                        |
| Drying system   | Exhaust air                   |
| Door opening [Ø] in mm                                | 520                           |
| Door opening angle in degrees                         | 180                           |
| Door hinge  | left                          |
| Convertible door hinging                              | •                             |
| Stainless steel honeycomb drum                        | Yes                           |
| Application   |                               |
| Suitable for the hotel and catering industry          | •                             |
| Suitable for retirement and care homes                | •                             |
| Suitable for facility management                      | •                             |
| Suitable for commercial laundries                     | •                             |
| Suitable for studs, riding schools and stables        | •                             |
| Suitable for universities, nurseries, and schools     | •                             |
| Suitable for hospitals                                | •                             |
| Suitable for sports clubs                             | •                             |
| Suitable for beauty salons, spas, and fitness centres | •                             |
| Suitable for amusement parks & holiday complexes      | •                             |
| Suitable for state/community care facilities          | •                             |
| Performance data                                      |                               |
| Maximum evaporation capacity in l/hour                | 25.80                         |
| Specific energy consumption in kWh/kg                 | 0.49                          |
| Programme duration in min.                            | 25                            |
| Service life in drying cycles                         | 40000                         |
| Control system  |                               |
| Control system  | M Select Benchmark            |
| Programmability                                       | Setting of defined parameters |
| User interface  | Residual moisture controlled  |
| Max. delay start in h                                 | 24                            |
| Time left display                                     | •                             |
| Control panel with easy-to-understand symbols         | •                             |
| Standard electrical connection                        |                               |
| Heating type  | Electric                      |
| Electrical connection                                 | 3N AC 400V 50/60HZ            |
| Electric heater rating in kW                          | 27.00                         |
| Total connected load in kW                            | 28.20                         |
| Fuse rating in A                                      | 50                            |
| Possible voltage variant 1                            |                               |
| Electrical connection                                 | 3N AC 400V 60HZ               |
| Heater rating in kW                                   | 27.00                         |
| Total connected load in kW                            | 28.20                         |

## PDR 528 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516409243 / Material number: 11718340 / Old Material Number: 52528001EU

|   |                    |
|---|--------------------|
| Fuse rating in A                                | 50                 |
| <b>Dimensions and weight of dryer</b>           |                    |
| External dimensions, height in mm               | 1640               |
| External dimensions, width in mm                | 1206               |
| External dimensions, depth in mm                | 1019               |
| External dimensions, gross height in mm         | 1766               |
| External dimensions, gross width in mm          | 1390               |
| External dimensions, gross depth in mm          | 1108               |
| Net weight in kg                                | 243.3              |
| Gross weight in kg                              | 258                |
| Maximum floor load in N/m <sup>2</sup>          | 2799               |
| <b>Emissions data</b>                           |                    |
| Emission sound pressure level in the workplace  | 58 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h          | 3.30               |
| <b>Features</b>                                 |                    |
| Intelligent drum reversal                       | •                  |
| Axial airflow                                   | •                  |
| Large-surface fluff filter                      | •                  |
| PerfectDry                                      | •                  |
| SoftLift drum ribs                              | •                  |
| AirRecycling                                    | •                  |
| Communication slot                              | •                  |
| Emergency switch-off                            | •                  |
| Machine-independent accessories                 | •                  |
| <b>Connection options</b>                       |                    |
| Payment system (optional)                       | •                  |
| Optical interface for service access            | •                  |
| Peak load cut-out/energy management (optional)  | •                  |
| WiFi tumble dryer                               | •                  |
| Connector Box                                   | •                  |
| LAN module (optional)                           | •                  |
| <b>Standards, test certificates and symbols</b> |                    |
| CE  | •                  |
| VDE   | •                  |
| VDE-EMC   | •                  |
| Splash-proof safety rating IPX4                 | •                  |
| DVGW gas  | •                  |
| WEEE  | •                  |
| UKCA  | •                  |
| Complies with Machinery Directive 2006/42/EC    | •                  |