

PDR 944 [EL] Professional vented dryer, electric heating with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 800.00 I, load size32.0 kg-44.0 kg
- Unique, gentle fabric care honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516409281 / Material number: 11718380 / Old Material Number: 52944001EU

Construction type and version Front loader Range Performance Plus	
Range Performance Plus	
Front Iron grey	
Load size with a load ratio of 1:25 32.0	
Load size with a load ratio of 1:18 44.0	
Drum volume in I 800.00	
Drying system Exhaust air	
Door opening [Ø] in mm 520	
Door opening angle in degrees 180	
Door hinge left	
Convertible door hinging •	
Stainless steel honeycomb drum Yes	
Application	
Suitable for the hotel and catering industry •	
Suitable for retirement and care homes •	
Suitable for facility management •	
Suitable for dry cleaners •	
Suitable for commercial laundries •	
Suitable for fire brigades and rescue services •	
Suitable for studs, riding schools and stables •	
Suitable for universities, nurseries, and schools •	
Suitable for hospitals •	
Suitable for sports clubs •	
Suitable for beauty salons, spas, and fitness centres •	
Suitable for doctors' and dentists' practices •	
Suitable for the petrochemicals industry •	
Suitable for the food-processing industry •	
Suitable for amusement parks & holiday complexes •	
Suitable for state/community care facilities •	
Performance data	
Maximum evaporation capacity in I/hour 37.20	
Specific energy consumption in kWh/kg 0.52	
Programme duration in min. 28	
Service life in drying cycles 40000	
Control system	
Control system M Touch Pro	
Programmability programmable	
User interface Residual moisture controlled	
Max. delay start in h	
Time left display •	
Programme sequence indicator •	
Selectable display languages •	
Standard electrical connection	
Osarida a dioutiful confidence	
)HZ
Heating type Electric)HZ
Heating type Electric Electrical connection 3N AC 400V 50/60)HZ



PDR 944 [EL] Professional vented dryer, electric heating with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516409281 / Material number: 11718380 / Old Material Number: 52944001EU

Dimensions and weight of dryer External dimensions, height in mm 1206 External dimensions, width in mm 1206 External dimensions, gross height in mm 1385 External dimensions, gross height in mm 1766 External dimensions, gross width in mm 1390 External dimensions, gross width in mm 1474 Net weight in kg 294.3 Gross weight in kg 312 Maximum floor load in N/m² 3535 Emissions data 8 Emission sound pressure level in the workplace 63 dB(A) re 20 μPa Heat dissipation into the room in MJ/h 4.00 Features Intelligent drum reversal Axial airiflow • Large-surface fluff filter • PerfectDry • SoftLiff drum ribs • AirRecycling Flex • Communication slot • Emergency switch-off • Machine-independent accessories • Connection options • Payment system (optional) • Optical interf	D:	
External dimensions, width in mm	Dimensions and weight of dryer	10.10
External dimensions, depth in mm External dimensions, gross height in mm External dimensions, gross width in mm 1390 External dimensions, gross width in mm 1390 External dimensions, gross width in mm 1474 Net weight in kg 294.3 Gross weight in kg 312 Maximum floor load in N/m² Brissions data Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h 4.00 Features Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over alse [number] Over alse [number] Synthetic cluvets [number] Down duvets [number] A Synthetic pillows [number] Down duvets [number] Bown duvets [number] Cotton mops, 50 cm [number] Microfibre mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE VDE VDE Splash-proof safety rating IPX4		
External dimensions, gross height in mm External dimensions, gross width in mm External dimensions, gross depth in mm 1390 External dimensions, gross depth in mm 1474 Net weight in kg 294.3 Gross weight in kg 312 Maximum floor load in N/m² 35355 Emissions data Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h 4.00 Features Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over Jakets [number] Over Jakets [number] Over Jakets [number] A Synthetic duvets [number] B Down duvets [number] A Synthetic pillows [number] A Synthetic pillows [number] A Synthetic pillows [number] B Down duvets [number] Cotton mops, 40 cm [number] A Synthetic pillows [number] A Synthetic pillows [number] B Cotton mops, 50 cm [number] A Synthetic pillows [number] A Synthetic pillows [number] B Standards, test certificates and symbols CE VDE VDE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4	· · · · · · · · · · · · · · · · · · ·	
External dimensions, gross width in mm External dimensions, gross depth in mm 1474 Net weight in kg 294.3 Gross weight in kg 312 Maximum floor load in N/m² 3535 Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h 4.00 Features Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Over jackets [number] Down duvets [number] Down duvets [number] Down duvets [number] Down duvets [number] Down Jillows [number] Air Box (Durmber) Box (Durmber) Down duvets [number] Synthetic outloss, 40 cm [number] Down duvets [number] Down flows [number] Standards, test certificates and symbols CE VDE VDE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4		
External dimensions, gross depth in mm Net weight in kg Gross weight in kg Asimum floor load in N/m² 3535 Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h Heat dissipation		
Net weight in kg Gross weight in kg Asximum floor load in N/m² Brissions data Emissions sound pressure level in the workplace Heat dissipation into the room in MJ/h Features Hitelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Over jackets [number] Over jackets [number] Over jackets [number] Agnumber] Owen duvets [number] Agnumber] Owen duvets [number] Agnumber] Owen jackets [number] Agnumber] Over jackets [number] Agnumber] Over jackets [number] Agnumber] Over jackets [number] Agnumber] Over jackets [number] Agnumber] Agnu	External dimensions, gross width in mm	1390
Gross weight in kg Maximum floor load in N/m² Emissions data Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h Features Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Oyer jackets [number] Synthetic duvets [number] Down duvets [number] A Synthetic pillows [number] Down duvets [number] A Some passible in the service and serv	External dimensions, gross depth in mm	1474
Maximum floor load in N/m² 3535 Emissions data 63 dB(A) re 20 μPa Heat dissipation into the room in MJ/h 4.00 Features Intelligent drum reversal Axial airflow • Large-surface fluff filter • PerfectDry • SoftLift drum ribs • AirRecycling Flex • Communication slot • Emergency switch-off • Machine-independent accessories • Connection options • Payment system (optional) • Optical interface for service access • Peak load cut-out/energy management (optional) • WiFi tumble dryer • Connector Box • LAN module (optional) • Capacities • Respirator masks [number] 16 Overalls [number] 9 Synthetic duvets [number] 4 Synthetic duvets [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 18	Net weight in kg	294.3
Emissions data Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h Features Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over alas [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down duvets [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4	Gross weight in kg	312
Emission sound pressure level in the workplace Heat dissipation into the room in MJ/h Features Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down duvets [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE-EMC Splash-proof safety rating IPX4 • A displace in the workplace • A (0,0) • • A (0,	Maximum floor load in N/m ²	3535
Heat dissipation into the room in MJ/h Features Intelligent drum reversal Axial airflow	Emissions data	
Intelligent drum reversal Axial airflow Earge-surface fluff filter PerfectDry Earge-surface fluff filter Earge-surface f	Emission sound pressure level in the workplace	63 dB(A) re 20 µPa
Intelligent drum reversal Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) Wifi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over alsa [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down pillows [number] Down pillows [number] A Down pillows [number] Down pillows [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4	Heat dissipation into the room in MJ/h	4.00
Axial airflow Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Synthetic pillows [number] AB Cloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE-EMC Splash-proof safety rating IPX4	Features	
Large-surface fluff filter PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down duvets [number] Synthetic pillows [number] Down pillows [number] Cotton mops, 40 cm [number] Microfibre mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE-EMC Splash-proof safety rating IPX4	Intelligent drum reversal	•
PerfectDry SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over alsc [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Bown duvets [number] Cotton mops, 50 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4 • Communication • • • Communication • • • • Communication • • • • Connector So • • - - - - - - - - - - - -	Axial airflow	•
SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Synthetic pillows [number] Down pillows [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4	Large-surface fluff filter	•
SoftLift drum ribs AirRecycling Flex Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Synthetic pillows [number] Down pillows [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4	PerfectDry	•
Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] 9 Synthetic duvets [number] Down duvets [number] Down pillows [number] 8 Cloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Microfibre mops, 50 cm [number] Summer horse blankets [number] Standards, test certificates and symbols CE VDE VDE VDE-EMC Splash-proof safety rating IPX4	SoftLift drum ribs	•
Communication slot Emergency switch-off Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] 9 Synthetic duvets [number] Down duvets [number] Down pillows [number] 8 Cloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Microfibre mops, 50 cm [number] Summer horse blankets [number] Standards, test certificates and symbols CE VDE VDE VDE-EMC Splash-proof safety rating IPX4	AirRecycling Flex	•
Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down pillows [number] Down pillows [number] Eloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 40 cm [number] Summer horse blankets [number] Standards, test certificates and symbols CE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4		•
Machine-independent accessories Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down pillows [number] Down pillows [number] Eloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 40 cm [number] Summer horse blankets [number] Standards, test certificates and symbols CE VDE VDE VDE VDE-EMC Splash-proof safety rating IPX4	Emergency switch-off	•
Connection options Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Overalls [number] Over jackets [number] Synthetic duvets [number] Own duvets [number] Down duvets [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4		•
Payment system (optional) Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Synthetic duvets [number] Own duvets [number] Down duvets [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4	·	
Optical interface for service access Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] 16 Overalls [number] 6 Over jackets [number] 9 Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 168 Cotton mops, 50 cm [number] 168 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE VDE VDE-EMC Splash-proof safety rating IPX4		•
Peak load cut-out/energy management (optional) WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over jackets [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Cloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 50 cm [number] Microfibre mops, 50 cm [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4		•
WiFi tumble dryer Connector Box LAN module (optional) Capacities Respirator masks [number] Over alls [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down duvets [number] Ciloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 40 cm [number] Microfibre mops, 50 cm [number] Summer horse blankets [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4	<u> </u>	•
Connector Box LAN module (optional) Capacities Respirator masks [number] Overalls [number] Over jackets [number] Synthetic duvets [number] Down duvets [number] Down duvets [number] Cloths, 22 g [number] Cotton mops, 40 cm [number] Microfibre mops, 40 cm [number] Microfibre mops, 50 cm [number] Microfibre mops, 50 cm [number] Summer horse blankets [number] Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4		•
LAN module (optional) Capacities Respirator masks [number] 16 Overalls [number] 6 Over jackets [number] 9 Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE VDE Splash-proof safety rating IPX4		•
Capacities 16 Respirator masks [number] 6 Over alls [number] 9 Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		•
Respirator masks [number] 16 Overalls [number] 6 Over jackets [number] 9 Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols 6 CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Overalls [number] 6 Over jackets [number] 9 Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols 6 CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 •	·	16
Over jackets [number] 9 Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols 6 CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Synthetic duvets [number] 4 Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 267 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols 6 CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Synthetic pillows [number] 8 Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 267 Microfibre mops, 40 cm [number] 287 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Down duvets [number] 4 Down pillows [number] 8 Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 267 Microfibre mops, 40 cm [number] 28 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Down pillows [number] 8		
Cloths, 22 g [number] 727 Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Cotton mops, 40 cm [number] 168 Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Cotton mops, 50 cm [number] 145 Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Microfibre mops, 40 cm [number] 267 Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols CE VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Microfibre mops, 50 cm [number] 188 Summer horse blankets [number] 5 Standards, test certificates and symbols • CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Summer horse blankets [number] 5 Standards, test certificates and symbols CE • VDE • VDE-EMC • Splash-proof safety rating IPX4 •		
Standards, test certificates and symbols CE VDE VDE-EMC Splash-proof safety rating IPX4		
CE VDE VDE-EMC Splash-proof safety rating IPX4 •		5
VDE•VDE-EMC•Splash-proof safety rating IPX4•	•	
VDE-EMC • Splash-proof safety rating IPX4 •		<u> </u>
Splash-proof safety rating IPX4		
		<u> </u>
WEEE •		•
		•
UKCA •	UKCA	•



PDR 944 [EL] Professional vented dryer, electric heating with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516409281 / Material number: 11718380 / Old Material Number: 52944001EU

Complies with Machinery Directive 2006/42/EC