

## PDR 944 [HW]

Professional vented dryer, heated with hot water  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 800.00 l, load size 53 (24.0) lb (kg) kg–32.0 kg
- Unique, gentle fabric care – honeycomb drum
- Excellent energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516409304 / Material number: 11718400 / Old Material Number: 52944006EU

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Iron grey
Load size with a load ratio of 1:32	53 (24.0) lb (kg)
Load size with a load ratio of 1:25	32.0
Drum volume in l	800.00
Drying system	Hot water
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Specific energy consumption in kWh/kg	0.47
Programme duration in min.	62
Service life in drying cycles	40000
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard electrical connection	
Heating type	Hot water
Electrical connection	3N AC 400V 50/60HZ
Electric heater rating in kW	0.00
Heater rating, hot water in kW	12.50
Total connected load in kW	1.70
Fuse rating in A	10

## PDR 944 [HW]

Professional vented dryer, heated with hot water  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516409304 / Material number: 11718400 / Old Material Number: 52944006EU

Maximum water intake temperature in °C	90
<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	1640
External dimensions, width in mm	1206
External dimensions, depth in mm	1385
External dimensions, gross height in mm	1766
External dimensions, gross width in mm	1390
External dimensions, gross depth in mm	1474
Net weight in kg	326.3
Gross weight in kg	344
Maximum floor load in N/m <sup>2</sup>	3848
<b>Emissions data</b>	
Emission sound pressure level in the workplace	63 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	4.00
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecyclingPlus	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Respirator masks [number]	16
Overalls [number]	6
Over jackets [number]	9
Synthetic duvets [number]	4
Synthetic pillows [number]	8
Down duvets [number]	4
Down pillows [number]	8
Cloths, 22 g [number]	727
Cotton mops, 40 cm [number]	95
Cotton mops, 50 cm [number]	82
Microfibre mops, 40 cm [number]	150
Microfibre mops, 50 cm [number]	131
Summer horse blankets [number]	5
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•

PDR 944 [HW]

Professional vented dryer, heated with hot water  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516409304 / Material number: 11718400 / Old Material Number: 52944006EU

UKCA

Complies with Machinery Directive 2006/42/EC

•  
•