

K 7793 C

Built-in refrigerator

with PerfectFresh Active, FlexiLight 2.0 and FlexiTray for maximum convenience.



- Fresh 5x longer with active humidification – PerfectFresh Active
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- Uniform temperature distribution inside the appliance – DynaCool
- Easy to remove items thanks to pivotable glass shelf – FlexiTray
- Door shelf heights can be adjusted individually



EAN: 4002516413103 / Material number: 11729610 / Old Material Number: 36779300GB

<b>Appliance category</b>	
Refrigerator	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Refrigeration section lighting	FlexiLight 2.0
Fan lighting	•
Freshness system lighting	•
<b>User convenience</b>	
Networking with Miele@home	•
Freshness system	PerfectFresh Active
Active humidification in top drawer	•
Fine adjustment inner door	•
ComfortClean	•
DynaCool	•
ComfortSize	•
SoftClose	•
SelfClose	•
<b>Controls</b>	
Operating concept	FreshTouch
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
No. of temperature zones	2
Sabbath mode	•
Party mode	•
Holiday mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	4
of which illuminated	3
Chrome-plated metal bottle rack	•
No. of crisper drawers	3
CompactCase	•
FlexiTray	•
Number of inner door racks for tinned food	3
Door rack for bottles	2
Door shelves	5
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	C
Annual energy consumption in kWh	99.90
Energy consumption in 24 h in kWh	0.27
<b>Safety</b>	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•

K 7793 C

Built-in refrigerator

with PerfectFresh Active, FlexiLight 2.0 and FlexiTray for maximum convenience.




EAN: 4002516413103 / Material number: 11729610 / Old Material Number: 36779300GB

Technical data	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	544
Weight in kg	70.3
Max. door front weight – refrigerator, in kg	26
Climate class	SN-T
Refrigerator compartment in l	296
including PerfectFresh zone in l	98
4* freezer compartment in l	0
Total usable capacity in l	296
Noise class (A–D)	B
Sound power in dB(A) re 1 pW	32
Current consumption (mA)	0
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.2
Replacing lamps	Customer Service
Accessories supplied	
Egg tray	•
PerfectFresh organisation box	•

## K 7793 C


### Built-in refrigerator

with PerfectFresh Active, FlexiLight 2.0 and FlexiTray for maximum convenience.



K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7743D, K7744E, K7773D, K7774D, built-in (footnote\*) (drawings)

\*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.



K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7743D, K7744E, K7773D, K7774D, side view (installation drawings)