

APWM 050

Dispenser pumps

with dispensing control for two liquid dispensing agents.



- Suitable for use with Miele Professional washing machines
- Optimised hose replacement thanks to quick-coupling system
- Ideal for use with Miele ProCare Tex process chemicals
- Can be used with suction lances for canisters of different sizes
- Programme selector and alarm system for empty can be added

EAN: 4002516419372 / Material number: 11733450 / Old Material Number: 59510050NER

Product category	
Washing machines	•
Machine/accessory category	
PW 413	•
PW 418	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 6080	•
PW 6088	•
PW 6163	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PWT 6089	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 509	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•
PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
Product category	
Dispenser system	•
Product properties	
Material	Plastic
Colour	Black/white
Dimensions and weight	
External dimensions, net height in mm	285
External dimensions, net width in mm	190
External dimensions, net depth in mm	166
External dimensions, gross height in mm	270
External dimensions, gross width in mm	270
External dimensions, gross depth in mm	350

APWM 050
Dispenser pumps
with dispensing control for two liquid dispensing agents.



EAN: 4002516419372 / Material number: 11733450 / Old Material Number: 59510050NER

Net weight [kg]	3.85
Gross weight in kg	4.30