

PRI 217 [EL SOM STW]

Rotary ironer, electrically heated

with the latest controls and steel wool padding for marine applications.



- Performance 60.0 kg/h*, roller diameter 250 mm, working width 1660 mm
- Ideal ergonomics – height-adjustable and optional plinth
- State-of-the-art controls – Touch display
- Selection of the most important settings – favourite programmes
- Perfect rotary ironing performance – flexibly positioned heater plate

* With 25 % residual moisture – performance data according to DIN 11902: the achievable ironing performance depends on overall conditions such as, for example, the type of laundry and the experience of the operator.


EAN: 4002516423041 / Material number: 11744760 / Old Material Number: 53217011SOM

| Construction type and version | |
|--|---|
| Construction type | Laundry infeed and outfeed at the front |
| Can be set up against a wall | • |
| Range | Professional |
| Outer casing | Iron grey |
| Roller diameter in mm | 250 |
| Working width in mm | 1660 |
| Heater plate material | Aluminium |
| Padding | Supple steel wool, Leaf-spring padding (option) |
| Ironer cover | ARAMID needle-felt cloth |
| Application | |
| Suitable for offshore use | • |
| Suitable for marine use | • |
| Performance data | |
| Max. ironing performance at 25 % residual moisture in kg/h | 60.0 |
| Tested operating hours | 20000 |
| Control system | |
| Control system | Touch display |
| Touch display (optional) | Touch-Display PRI |
| Programme setting | Setting of defined programme parameters |
| Minimum ironing speed, controlled in m/min | 1.5 |
| Maximum ironing speed, controlled in m/min | 4.5 |
| Adjustable temperature | Infinitely variable |
| Standard electrical connection | |
| Heating type | Electric |
| Electrical connection | 3 AC 230V 50-60HZ |
| Electric heater rating in kW | 11.00 |
| Total connected load in kW | 11.60 |
| Fuse rating in A | 50 |
| Dimensions and weight | |
| External dimensions, height in mm | 1110 |
| External dimensions, width in mm | 2238 |
| External dimensions, depth in mm | 650 |
| External dimensions, gross height in mm | 1414 |
| External dimensions, gross width in mm | 2400 |
| External dimensions, gross depth in mm | 860 |
| Net weight in kg | 189 |
| Gross weight in kg | 214 |
| Maximum floor load in N/m ² | 1890 |
| Emissions data | |
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 11.00 |
| Features | |
| Automatic finger guard | • |
| FlexControl footswitch | • |
| Feed-in board | • |
| Pick-off bands | • |
| Laundry box | • |

PRI 217 [EL SOM STW]

Rotary ironer, electrically heated

with the latest controls and steel wool padding for marine applications.



EAN: 4002516423041 / Material number: 11744760 / Old Material Number: 53217011SOM

| | |
|--|---|
| Favourite programme | • |
| Incorrect feed recognition | • |
| Air suspension | • |
| Pause function | • |
| High contact pressure | • |
| Clean and wax heater plate indicator (op | • |
| Plinth (optional) | • |
| Option of ironing when seated | • |
| APRI 319 care set for the heater plate included in the scope of delivery | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Peak load cut-out/energy management | • |
| Standards, test certificates and symbols | |
| VDE | • |
| CE | • |
| EAC | • |
| WEEE | • |
| VDE-EMC | • |
| RCM | • |
| Splash-proof IPX0 | • |
| UKCA | • |
| Complies with Machinery Directive 2006/42/EC | • |