

PWM 916 [SD DV DD ST]

Professional washing machine, steam heating (direct)

with detergent drawer, suds tap, M Touch Pro Plus – freely programmable.



- Drum volume 140 l, load size 16.0 kg
- Top cleaning & consumption values – innovative Miele technology
- Ideal operation thanks to colour touch display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and WiFi

EAN: 4002516436003 / Material number: 11779800 / Old Material Number: 51916024GB

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Control panel colour	Stainless steel
Maximum load with a load ratio of 1:9 in kg	16.0
Load ratio	1:9
Load in kg	16.0
Drum volume in l	140
Door opening [Ø] in mm	415
Door opening angle in degrees	180
Door hinge	right
Automatic door lock	•
Innovative suds container	•
Maintenance-free motor with frequency converter	•
Patented honeycomb drum 2.0	•
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for launderettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6.20
Specific energy consumption for cold water connection in kWh/kg	0.13
Specific water consumption for hot water connection in l/kg	5.90
Water consumption with cold water connection in l	99.2
Water consumption for cold water connection in Mops standard 60 °C programme in l	182.2
Energy consumption with cold water connection in kWh	2.00
Energy consumption for cold water connection in Mops standard 60 °C programme in kWh	3.21

PWM 916 [SD DV DD ST]

Professional washing machine, steam heating (direct)

with detergent drawer, suds tap, M Touch Pro Plus – freely programmable.



EAN: 4002516436003 / Material number: 11779800 / Old Material Number: 51916024GB

Programme duration in minutes with cold water connection	46
Water consumption with hot water connection in l	94.4
Water consumption in ECO programme with cold water connection in l	92.8
Energy consumption in ECO programme with cold water	1.50
Programme duration in minutes with cold water connection in ECO programme	33
Water consumption in ECO programme with hot water connection in l	91.2
Programme running time in minutes for Mops standard 60 °C programme with cold water connection	53
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	44
Residual moisture when processing cleaning cloths in %	25
Spin speed in rpm	1075
g factor	462
Tested operating hours	30000
Control system	
Control system	M Touch Pro Plus
Programmability	Freely programmable
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Option to enter weight prior to start of programme	•
Standard/target grp programmes	
Basic programmes	•
Dispensing	
Detergent drawer	3 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
Standard electrical connection	
Heating type	Direct steam
Electrical connection	3N AC 400V 50HZ
Steam heater rating in kW	27.00
Total connected load in kW	2.30
Fuse rating in A	16
Possible voltage variant 1	
Electrical connection	3N AC 400V 60HZ
Total connected load in kW	2.30
Fuse rating in A	16
Water connection/drainage	
Cold water [number]	3 x 1/2" hose w/ 3/4" union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Hard water (optional) [number]	2 x 1/2" w/ 3/4" union
Dump valve	DN 70
Steam connection	
NEMA Plug: Twist Lock L6-30	1/2"
Dimensions and weight	
External dimensions, height in mm	1450

PWM 916 [SD DV DD ST]

Professional washing machine, steam heating (direct)

with detergent drawer, suds tap, M Touch Pro Plus – freely programmable.

EAN: 4002516436003 / Material number: 11779800 / Old Material Number: 51916024GB

External dimensions, width in mm	962
External dimensions, depth in mm	835
External dimensions, gross height in mm	1585
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	1130
Net weight in kg	338.0
Gross weight in kg	358
Maximum floor load in N/m ²	5101
Emissions data	
Emission sound pressure level in the workplace	65 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	6.48
Features	
Patented pre-spin	•
Cloth reprocessing	•
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Efficient scoop-and-ladle ribs	•
EcoSpeed	•
Spring-in-spring system	•
Temperature monitoring	•
Sampling tap	•
Special heater element	•
Automatic load control+	•
Volumetric flow meter (optional)	•
Add laundry	•
Programme selection via colour frame	•
Emergency switch-off	•
Machine-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	92
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
Water recovery (optional)	•
LAN	•
WiFi	•
Connector Box	•
Capacities	
Respirator masks [number]	13
Helmets [number]	4
Overalls [number]	2
Over jackets [number]	3
Chemical protection suits [number]	1
Synthetic duvets [number]	1
Synthetic pillows [number]	3
Down duvets [number]	1
Down pillows [number]	3
Cloths, 22 g [number]	355
Cotton mops, 40 cm / 190 g [number]	82
Cotton mops, 50 cm / 220 g [number]	71

PWM 916 [SD DV DD ST]

Professional washing machine, steam heating (direct)

with detergent drawer, suds tap, M Touch Pro Plus – freely programmable.



EAN: 4002516436003 / Material number: 11779800 / Old Material Number: 51916024GB

Microfibre mops, 40 cm / 120 g [number]	130
Microfibre mops, 50 cm / 170 g [number]	91
Mops, office, 100 g [quantity]	160
Mops, stairway, 150 g [quantity]	105
Summer horse blankets [number]	3
Standards, test certificates and symbols	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•