

## PW 6243 [EL WEK]

Hygiene washing machine, electrically heated

Barrier machine for retirement and care homes as well as hospitals.



- Drum volume 240 l, load size 24.0 kg
- Wide variety of programmes – special disinfection programme
- Gentle laundry care thanks to the Miele honeycomb drum
- Particularly efficient – low water and energy consumption
- Perfect spinning results – residual moisture 46 %\*, g-factor360

\* Residual moisture specification relates to a hot rinse during the last rinse cycle.

EAN: 4002516446996 / Material number: 11812870 /

Old Material Number: 51624305ZER

### Construction type and version

Construction type	Hygiene washing machine
Range	Professional
Front	Iron grey
Load ratio	1:10
Load in kg	24.0
Drum volume in l	240
Door opening [W] in mm clean side	352
Door opening [H] in mm clean side	593
Door opening [W] in mm unclean side	352
Door opening [H] in mm unclean side	593
Door opening angle in degrees	153
Maintenance-free motor with frequency converter	•
Stainless steel honeycomb drum	•

### Application

Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for hospitals	•

### Performance data

Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for hot water connection in l/kg	10.63
Specific energy consumption for hot water connection in kWh/kg	0.09
Programme duration in minutes with cold water connection	68
Programme duration in minutes with cold water and hot water connection	53
Residual moisture with cold rinse in %	50
Residual moisture with hot rinse in %	46
Spin speed in rpm	975
g factor	360
Tested operating hours	30000

### Control system

Control system	Profitronic M
Programmability	Freely programmable
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•

### Standard/target grp programmes

Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for dry cleaners	•

## PW 6243 [EL WEK]

Hygiene washing machine, electrically heated

Barrier machine for retirement and care homes as well as hospitals.



EAN: 4002516446996 / Material number: 11812870 /

Old Material Number: 51624305ZER

Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for hospitals	•
Programmes for beauty clinics, spas, and fitness studios	•

### Dispensing

Detergent drawer	4 compartments
Liquid dispensing module (optional)	•
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•

### Standard electrical connection

Heating type	Electric
Electrical connection	3N AC 400V 50/60HZ
Heater rating in kW	24.00
Total connected load in kW	25.00
Fuse rating in A	50

### Water connection/drainage

Cold water [number]	2x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Hard water [number]	2 x 1/2" w/ 3/4" union
Dump valve	DN 70

### Dimensions and weight

External dimensions, height in mm	1718
External dimensions, width in mm	1384
External dimensions, depth in mm	1070
External dimensions, gross height in mm	1800
External dimensions, gross width in mm	1570
External dimensions, gross depth in mm	1138
Net weight in kg	820.0
Gross weight in kg	838
Maximum floor load in N	9808

### Emissions data

Emission sound pressure level in the workplace	71 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	9.00

### Features

Patented pre-spin	•
Cloth reprocessing	•
Imbalance monitoring	•
Temperature monitoring	•
Two indicator lights on the clean side	•
Automatic drum positioning and locking	•
Special heater element	•
Automatic load control+	•
Volumetric flow meter (optional)	•
Communication slot	•
Efficient fast spin cycle	•

## PW 6243 [EL WEK]

Hygiene washing machine, electrically heated

Barrier machine for retirement and care homes as well as hospitals.



EAN: 4002516446996 / Material number: 11812870 /

Old Material Number: 51624305ZER

Emergency switch-off	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	95
<b>Connection options</b>	
Optical interface for service access	•
Serial interface module RS 232 (optional)	•
Peak-load negotiation / energy management (optional)	•
Operating data acquisition	•
Water recovery (optional)	•
<b>Capacities</b>	
Synthetic duvets [number]	3
Synthetic pillows [number]	6
Down duvets [number]	3
Down pillows [number]	6
Cloths, 22 g [number]	545
Cotton mops, 40 cm / 190 g [number]	126
Cotton mops, 50 cm / 220 g [number]	109
Microfibre mops, 40 cm / 120 g [number]	200
Microfibre mops, 50 cm / 170 g [number]	141
<b>Standards, test certificates and symbols</b>	
CE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•