

TWW780WP Passion  
T1 heat-pump dryer:  
A+++ -10 % | 9 kg | M Touch | SteamFinish | SilenceDrum



- M Touch – simple control by tapping or swiping
- SteamFinishsmoothes and freshens up, saving you time during ironing
- The SilenceDrum\* reduces noise for much quieter drying
- Best care for delicate textiles – Miele dryer basket
- Complete app control of your tumble dryer with Miele@home\*\*

\* Patent EP 4 163 433

\*\* Additional digital offer from Miele & Cie. KG. All smart applications are made possible with the Miele@home system. The range of functions can vary depending on the model and the country.

**A+++**

EAN: 4002516475989 / Material number: 11876930 / Old Material Number: 12WW7802GB

Construction type	
Suitable for stacking	•
Side-by-side	•
Slot-in	•
Door hinge	left, Reversible
Convertible door hinging	•
Model	
Product brand	T1 White Edition
Heat pump dryer	•
Design	
Appliance colour	Lotus white
Control panel colour	Lotus white
Door design	Alu silver with chrome ring
Control panel version	5° inclined
Control type	Touch control
Display	MTouch
Drying results	
PerfectDry precision drying	•
FragranceDos <sup>2</sup> fragrance system	•
Intelligent drum reversal	•
Proven hygiene	•
Proven virus hygiene	•
Gentle laundry care	
SilenceDrum	•
Load in kg	9.0
User convenience	
Networking with Miele@home	•
Wash2Dry	•
Delay start up to 24 hours	•
Time left display	•
Time of day display	•
Programme sequence indicator	Yes
Drying assistant	•
Information text	•
Favourite programmes	•
Drum lighting	LED
MultiLingua	•
Acoustics package for the lowest sound emissions	•
Condensate container	•
Integrated condensed water drainage	•
AddLoad	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A+++
More economical than the threshold value (24) for energy efficiency class A+++	10%
Annual energy consumption in kWh	174
Duration in minutes in the standard programme	220
Noise in the Cottons programme with full load in db(A) re 1 pW	62
Condensation efficiency class	A

TWW780WP Passion  
 T1 heat-pump dryer:  
 A+++ -10 % | 9 kg | M Touch | SteamFinish | SilenceDrum



EAN: 4002516475989 / Material number: 11876930 / Old Material Number: 12WV7802GB

Energy consumption in kWh in the Cottons Normal dry standard programme with a full load	1.47
EcoFeedback	•
EcoDry technology	•
Maintenance-free heat exchanger	•
ProfiEco motor	•
<b>Drying programmes</b>	
Automatic plus	•
Cottons (coloureds)	•
Cottons arrow	•
Minimum iron	•
Delicates	•
Shirts	•
Silks handcare	•
Woollens handcare	•
Express	•
Denim	•
Outerwear	•
Proofing	•
Sportswear	•
Standard pillows	•
Large pillows	•
Cottons hygiene	•
Cool air	•
Warm air	•
Basket programme	•
Extra quiet	•
Pre-Ironing	•
Bed linen	•
Steam care	•
<b>Drying extras</b>	
Anti-crease	•
Gentle tumble	•
Freshen up	•
ECO	•
Buzzer	•
Quick	•
DryCare 40	•
DryFresh	•
PowerFresh	•
<b>Quality</b>	
Soft ribs	•
<b>Safety</b>	
PIN-Code	•
Empty out container indicator	•
Clean filter indication	•
Optical interface	•
<b>Technical data</b>	
Dimensions in mm (width)	596
Dimensions in mm (height)	850
Dimensions in mm (depth)	643

TWW780WP Passion  
 T1 heat-pump dryer:  
 A+++ -10 % | 9 kg | M Touch | SteamFinish | SilenceDrum



EAN: 4002516475989 / Material number: 11876930 / Old Material Number: 12WW7802GB


Appliance depth in mm with opened door	1077
Weight in kg	62
Total rated load in kW	1.10
Voltage in V	220-240
Fuse rating in A	13
Frequency in Hz	50
Length of supply lead in m	2.0
Contains fluorinated greenhouse gases	•
Hermetically sealed	•
Type of coolant	R134a
Refrigerant quantity in kg	0.48
Refrigerant global warming potential in CO <sub>2</sub> e	1430
Appliance global warming potential in CO <sub>2</sub> e	686.00
Replacing lamps	Service
<b>Accessories included</b>	
Fragrance flacon	•
Voucher for a second fragrance flacon	•
Voucher for a dryer basket	•

#### Available display languages


Available display languages via MultiLingua

bahasa malaysia, dansk, deutsch, english (AU), english (CA), english (GB), english (US), español, français (CA), français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portugês, русский, romãã, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,


TWW780WP Passion  
T1 heat-pump dryer:  
A+++ -10 % | 9 kg | M Touch | SteamFinish | SilenceDrum




T1 installation drawing, fascia 5 degree, measures in mm



T1 drawing, fascia 5 degree, measures in mm



T1 drawing, fascia 5 degree, with porthole, measures in mm



T1 drawing, fascia 5 degree, measures in mm