

## APWM 073

Dispensing adapter installation kit

for connecting dispensing pumps directly,  $\varnothing$  6 mm, max. capacity 9 kg.



- Suitable for hoses with 6 mm diameters
- For 9 kg Benchmark washing machines
- For 6 dispensing connections

EAN: 4002516589921 / Material number: 11902700 / Old Material Number: 59510073EU

<b>Product category</b>	
Washing machines	•
<b>Machine/accessory category</b>	
PWM 509	•
PWM 909	•
<b>Product category</b>	
Dispenser system	•
<b>Product properties</b>	
Material	Plastic
Colour	White
<b>Dimensions and weight</b>	
External dimensions, net height in mm	0
External dimensions, net width in mm	0
External dimensions, net depth in mm	0
External dimensions, gross height in mm	12
External dimensions, gross width in mm	100
External dimensions, gross depth in mm	150
Net weight [kg]	0.08
Gross weight in kg	0.09