

## PTD 901 [LIFT WES DOS]

Throughfeed dishwasher

with automatic hood function, integrated dispensing and softener.

EAN: 4002516485759 / Material number: 11917980 / Old Material Number: 61090124D



- Max. cleaning performance\*: 1296 plates/h
- For ergonomic working – automatic hood function
- Always the right programme – item-specific solutions
- Simple and flexible operation – full-touch display
- Optimum suds filtering- first-class filter system

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

| Construction type and version          |                        |
|--|------------------------|
| Construction type                      | Passthrough dishwasher |
| Range                                  | Professional           |
| Model                                  | Performance            |
| Wash system                            | Tank passthrough       |
| Number of levels                       | 1                      |
| Front                                  | Stainless steel        |
| Tank volume in l                       | 35.0                   |
| Application                            |                        |
| Suitable for retirement and care homes | •                      |
| Suitable for hospitals                 | •                      |
| Suitable for small restaurants/bars    | •                      |
| Suitable for hospitality industry      | •                      |
| Suitable for guesthouses               | •                      |
| Suitable for canteens                  | •                      |
| Suitable for child care facilities     | •                      |
| Suitable for universities and schools  | •                      |
| Suitable for fast food restaurants     | •                      |
| Suitable for sports clubs              | •                      |
| Performance data                       |                        |
| Tested virucidal efficacy              | •                      |
| Circulation pump Qmax in l/min.        | 300                    |
| Shortest programme duration in sec.    | 50                     |
| Maximum final rinse temperature in °C  | 90                     |
| Cleaning performance, plates/h         | 1296                   |
| Cleaning performance, glasses/h        | 3773                   |
| Cleaning performance, baskets/h        | 72                     |
| Service life in wash cycles            | 438000                 |
| Control system                         |                        |
| Control system                         | Electronic controls    |
| Programme selection                    | Full-touch display     |
| Automatic On/Off standby switch        | •                      |
| Programmes [number]                    | 4                      |
| Coloured programme sequence indicator  | •                      |
| Choice of display language             | •                      |
| Standard electrical connection         |                        |
| Electrical connection                  | 3N AC 380-415V 50HZ    |
| Heater rating in kW                    | 8.20                   |
| Tank heater rating in kW               | 2.50                   |
| Boiler heater rating in kW             | 10.80                  |
| Total connected load in kW             | 9.10                   |
| Fuse rating in A                       | 16                     |
| Length of mains connection cable in m  | 3.50                   |
| Possible voltage variant 1             |                        |
| Electrical connection                  | 3N AC 380-415V 50HZ    |
| Heater rating in kW                    | 10.80                  |
| Total connected load in kW             | 13.20                  |
| Fuse rating in A                       | 25                     |
| Possible voltage variant 2             |                        |
| Electrical connection                  | 3N AC 380-415V 50HZ    |

## PTD 901 [LIFT WES DOS]

Throughfeed dishwasher

with automatic hood function, integrated dispensing and softener.

EAN: 4002516485759 / Material number: 11917980 / Old Material Number: 61090124D



|  |                    |
|--|--------------------|
| Heater rating in kW  | 11.70              |
| Total connected load in kW   | 14.70              |
| Fuse rating in A   | 32                 |
| <b>Water connection/drainage</b>                                       |                    |
| Cold or hot water [number]   | 1                  |
| Required flow pressure in bar  | 1.00-6.00          |
| Drain pump [DN]  | 19                 |
| Drain pump head height from floor level, max. in c                     | 65                 |
| Booster pump   | •                  |
| Integrated water softener  | •                  |
| Maximum water hardness in mmol/l                                       | 5.35               |
| Water consumption per wash cycle in l                                  | 2.20               |
| Length of water inlet hose in cm                                       | 150                |
| Length of water drain hose in cm                                       | 150                |
| <b>Dimensions and weight</b>   |                    |
| External dimensions with closed hood, height                           | 1535               |
| External dimensions with opened hood, height                           | 2010               |
| External dimensions, net width in mm                                   | 635                |
| External dimensions, net depth in mm                                   | 750                |
| External dimensions, gross height in mm                                | 1660               |
| External dimensions, gross width in mm                                 | 770                |
| External dimensions, gross depth in mm                                 | 880                |
| Usable space in wash cabinet, height in mm                             | 440                |
| Usable space in wash cabinet, width in mm                              | 540                |
| Usable space in wash cabinet, depth of lower basket in mm              | 500                |
| Usable space in wash cabinet, depth in mm                              | 550                |
| In-feed height above floor in mm                                       | 850                |
| Net weight [kg]  | 141                |
| Gross weight in kg   | 155                |
| Maximum floor load in N/m <sup>2</sup>                                 | 2100               |
| <b>Emissions data</b>  |                    |
| Emissions – sound pressure at workplace                                | 62 dB(A) re 20 µPa |
| <b>Programmes</b>  |                    |
| Programme for light soiling  | •                  |
| Programme for normal soiling   | •                  |
| Programme for heavy soiling  | •                  |
| Additional programme options   | •                  |
| Wash ware specific   | •                  |
| Soak   | •                  |
| Self-cleaning  | •                  |
| Descaling  | •                  |
| Basic cleaning   | •                  |
| <b>Basket design</b>   |                    |
| Without baskets  | •                  |
| <b>Features</b>  |                    |
| Integrated dispensing pump/dispensing module for rinsing agent         | •                  |
| Integrated dispensing pump/dispensing module for liquid cleaning agent | •                  |
| Wash cabinet made from high-quality stai                               | •                  |
| Spray arm monitor for all spray arms                                   | •                  |
| Automatic hood function  | •                  |

PTD 901 [LIFT WES DOS]

Throughfeed dishwasher

with automatic hood function, integrated dispensing and softener.