

PWM 508 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 8.0 kg in 59 min.



- Drum volume 73 I, load size 8.0 kg
- 22 % less water consumption and 28 % less energy consumption^{*}
- Tested for intensive use unparalleled Miele quality
- Language-neutral fascia panel with rotary control M Select
- Thorough cleaning with professional wash programmes

*Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.



EAN: 4002516532903 / Material number: 11944640 / Old Material Number: 51508153GB

Construction type and design	
Construction type	Front-loader, stackable
Range	Performance
Front	Lotus white
Control panel colour	Stainless steel
Load in kg	8.0
Orum volume in I	73
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel	•
Application	
Suitable for the hotel and catering industry	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in I/	6.40
Specific energy consumption for cold water connection in kWh/kg	0.13
Specific water consumption for hot water connection in I/kg	6.00
Specific energy consumption for hot water connection in kWh/kg	0.06
Nater consumption with cold water connection in I	51.0
Energy consumption with cold water connection in kW	1.05
Programme duration in minutes with cold water connection	69
Vater consumption with hot water connection in I	48.0
nergy consumption with hot water connection in kW	0.50
Programme duration in minutes with cold water and hot water connection	59
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
	704



PWM 508 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 8.0 kg in 59 min.



EAN: 4002516532903 / Material number: 11944640 / Old Material Number: 51508153GB

Controls	
Control system	M Select
Programmability	programmable
Max. delay start in h	24
Time left display	
Programme sequence indicator	
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	`
Dispensing Detergent drawer	2 comportments
Detergent drawer	3 compartments
CapDosing	
Flexible dispensing adapter (optional)	•
Maximum number of connections for liquid dispenser	6
pumps [number]	•
Empty sensor Standard electrical connection	_
	Flantin
Heating type	Electric
Electrical connection	230V~
Heater rating in kW	2.65
Total connected load in kW	2.85
Fuse rating in A	13
Possible voltage variant 1	
Electrical connection	2N~ 400V 50HZ
Heater rating in kW	5.30
Total connected load in kW	5.50
Fuse rating in A	13
Water connection/drainage	
Cold water [number]	1x 1/2" hose w/ 3/4" th.
Hat water for order 2	union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain numn	DN 22
Drain pump	DIN 22
Dimensions and weight	050
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	714
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	103.0
Gross weight in kg	107
Maximum floor loading in N	2820
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 μPa
Heat dissipation into the room in MJ/h	1.00
Features	
3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
COMMITTED CHAIR CONTROL CONTRO	
Hard-wearing stainless-steel flange	•
	•



PWM 508 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and programmes specific to the target group. Performance 8.0 kg in 59 min.



EAN: 4002516532903 / Material number: 11944640 / Old Material Number: 51508153GB

Pre-ironing	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Machine-independent accessories	•
Efficiency and sustainability	
Load size for the "Eco 40-60" programme in kg	8.0
Energy efficiency class (A–G)	A
Spin efficiency class (A–G)	A
Weighted energy consumption per 100 cycles in the "Eco 40–60" programme in kWh	47
Weighted water consumption per cycle in the "Eco 40–60" programme in I	47
Airborne noise emission rating (spin cycle) (A–D)	A
Airborne noise emission during spin cycle in dB(A) re 1 pW	72
Airborne noise emission during spin cycle in dB(A) re 1 pW	219
Recycling rate in %	95
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi	•
WiFiConn@ct	•
Standards, certs, symbols	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WRAS	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•