

## PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.



- Drum volume 100 l, maximum load size 11.0 kg
- 14 % less water consumption and 50 % less energy consumption\*
- Maximum user convenience with colour touch display – M Touch Pro
- Perfect spinning results – residual moisture 50 %\*\*, g-factor370
- Connected for the future using LAN and WiFi

\* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.

\*\* Residual moisture specification relates to a hot rinse during the last rinse cycle.

EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

Construction type and version	
Construction type	Front loader
Range	Performance
Front	Iron grey
Control panel colour	Stainless steel
Maximum load with a load ratio of 1:9 in kg	11.0
Load ratio	1:9
Load in kg	11.0
Drum volume in l	100
Door opening [Ø] in mm	370
Door opening angle in degrees	180
Door hinge	right
Automatic door lock	•
Maintenance-free synchronous motor	•
Honeycomb drum	•
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	7.10
Specific energy consumption for cold water connection in kWh/kg	0.12
Specific water consumption for hot water connection in l/kg	6.90
Specific energy consumption for hot water connection in kWh/kg	0.03
Water consumption with cold water connection in l	78.4
Energy consumption with cold water connection in kW	1.37
Programme duration in minutes with cold water connection	57
Water consumption with hot water connection in l	75.7
Energy consumption with hot water connection in kW	0.32
Programme duration in minutes with cold water and hot water connection	52
Water consumption in ECO programme with cold water connection in l	67.8
Energy consumption in ECO programme with cold water	0.87
Programme duration in minutes with cold water connection in ECO programme	34
Water consumption in ECO programme with hot water connection in l	68.3
Energy consumption in ECO programme with hot water	0.13
Programme duration in minutes with cold water and hot water connection in ECO programme	33
Residual moisture with cold rinse in %	54
Residual moisture with hot rinse in %	50
Spin speed in rpm	1100
g factor	370
Tested operating hours	30000

## PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.



EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

<b>Control system</b>	
Control system	M Touch Pro
Programmability	programmable
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
<b>Standard/target grp programmes</b>	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for laundrettes	•
Programmes for residential homes and apartments	•
Programmes for dry cleaners	•
Programmes for commercial laundries	•
Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for universities, nurseries, and school	•
Programmes for hospitals	•
Programmes for fast food restaurants	•
Programmes for camp sites	•
Programmes for sports clubs	•
Programmes for beauty clinics, spas, and fitness studios	•
Programmes for domestic use	•
Programmes for doctors' and dentists' practices	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
Flexible dispensing adapter (optional)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3 AC 440V 60HZ
Heater rating in kW	6.05
Total connected load in kW	6.30
Fuse rating in A	16
<b>Possible voltage variant 1</b>	
Electrical connection	3 AC 480V 60HZ
Heater rating in kW	7.20
Total connected load in kW	7.45
Fuse rating in A	16
<b>Possible voltage variant 2</b>	
Electrical connection	3 AC 400V 60 HZ
Heater rating in kW	5.00
Total connected load in kW	5.25
Fuse rating in A	16

## PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.

EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Grey water (optional) [number]	1 x 1/2" w/ 3/4" union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, height in mm	1020
External dimensions, width in mm	700
External dimensions, depth in mm	818
External dimensions, gross height in mm	1214
External dimensions, gross width in mm	750
External dimensions, gross depth in mm	917
Net weight in kg	154.0
Gross weight in kg	167
Maximum floor load in N/m <sup>2</sup>	2636
<b>Emissions data</b>	
Emission sound pressure level in the workplace	61 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2.80
<b>Features</b>	
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Temperature monitoring	•
Special heater element	•
Automatic load control+	•
Flow meter	•
Add laundry	•
Programme selection via colour frame	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	91
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN	•
WiFi	•
Connector Box	•
<b>Capacities</b>	
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down duvets [number]	1
Down pillows [number]	2
<b>Standards, test certificates and symbols</b>	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WEEE	•
EAC	•

PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.



EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

Complies with Machinery Directive 2006/42/EC

•