

Classic C1 Flex - SBAF5  
Cylinder vacuum cleaner  
with telescopic tube for convenient vacuuming at an attractive entry-level price



- Energy-efficient vacuuming – 800 W
- Versatile applications – universal floorhead
- Long flexible crevice nozzle for cleaning narrow gaps
- Particularly lightweight – 5.8 kg with vacuuming accessories
- Effortless vacuuming of large areas with a 9 m operating radius

EAN: 4002516553878 / Material number: 12029920 / Old Material Number: 41BAF531GB

<b>Construction type</b>	
Cylinder vacuum cleaner with dustbag	•
Product brand	Classic C1
Motor type	PowerLine
Product type	SBAF5
Appliance Colour	Lotus white
<b>User convenience</b>	
Electronic suction power control	6-stage rotary selector
XXL handle	•
Suction tube	Comfort compact telescopic tube
Park system for pauses during vacuuming	•
Park system	One side
<b>Efficiency and sustainability</b>	
Nominal power consumption in W	800
<b>Mobility</b>	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	9
Cable length in m	5.5
<b>Filter system</b>	
Vacuum cleaner bag type	HyClean GN
Dustbag volume in l	4.5
Dustbag change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
<b>Safety</b>	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
<b>Technical data</b>	
Max. power	800
Volume in dB	79.0
Diameter in mm	463
Height in mm	221
Weight in kg	5.5
<b>Accessories supplied</b>	
Three-piece accessory set	On VarioClip
Upholstery nozzle	•
Crevice nozzle	•
Extra long, flexible crevice nozzle SDF 20	•
Dusting brush with synthetic bristles	•
Floorhead SBD 355-3	•
Filter	AirClean filter
Cleaning tool	No