

Compact C2 - SDRF5
Cylinder vacuum cleaner
Space-saving storage thanks to the Compact System.



- Versatile applications – universal floorhead
- Power Efficiency Motor with improved efficiency
- Retains even the smallest particles – AirClean+ filter
- Lightweight – 6.5 kg with vacuuming accessories
- Extremely convenient height adjustment thanks to a Comfort telescopic tube.

EAN: 4002516553960 / Material number: 12030370 / Old Material Number: 41DRF510GB

Construction type	
Cylinder vacuum cleaner with dustbag	•
Product brand	Compact C2
Motor type	PowerLine
Product type	SDRF5
Appliance Colour	Marine blue
User convenience	
Electronic suction power control	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
XXL handle	•
Silence system	•
Suction tube	Comfort Compact telescopic tube
Park system for pauses during vacuuming	•
Park system	on both sides, Compact
Comfort cable rewind	•
Efficiency and sustainability	
Nominal power consumption in W	890
Mobility	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	11
Cable length in m	7.5
Filter system	
Vacuum cleaner bag type	HyClean FJM
Dustbag volume in l	3.5
Dustbag change indicator	•
Exhaust filter	AirClean Plus filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
Technical data	
Max. power	890
Volume in dB	79.0
Width in mm	425
Height in mm	230
Weight in kg	6.5
Accessories included	
Three-piece accessory set	On VarioClip
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Floorhead SBD 355-3	•
Filter	AirClean Plus filter
Cleaning tool	No