

Complete C3 Flex
Cylinder vacuum cleaner
with highly efficient motor for energy-efficient vacuuming.



- Versatile applications – universal floorhead
- Long flexible crevice nozzle for cleaning narrow gaps
- Easy cleaning of larger areas thanks to 12 m operating radius
- Power Efficiency Motor with improved efficiency
- Convenient and versatile with three integrated accessories

EAN: 4002516554585 / Material number: 12031900 /
Old Material Number: 41GDF532GB

Construction type	
Cylinder vacuum cleaner with dustbag	•
Product brand	Complete C3
Motor type	PowerLine
Product type	SGDF5
Appliance Colour	Curry yellow
User convenience	
Electronic suction power control	+/- footswitches
Illuminated power indicator	•
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Suction tube	Comfort telescopic tube
Park system for pauses during vacuuming	•
Park system	on both sides
Comfort cable rewind	•
Mobility	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	12
Cable length in m	8.5
Filter system	
Vacuum cleaner bag type	HyClean GN
Dustbag volume in l	4.5
Dustbag change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
All-round furniture protection strip	•
Technical data	
Power	890
Volume in dB	77.0
Width in mm	496
Height in mm	227
Weight in kg	7.3
Accessories included	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Crevice nozzle	•
Extra-long, flexible crevice nozzle	•
Dusting brush with synthetic bristles	•
Floorhead	•