

## Complete C3

### Cylinder vacuum cleaner

With maximum suction power and foot controls for thorough, convenient vacuuming.



- Power Efficiency Motor with improved efficiency
- Versatile applications – universal floorhead
- Convenient and versatile with three integrated accessories
- Extremely convenient height adjustment thanks to a Comfort telescopic tube.
- Easy cleaning of larger areas thanks to 12 m operating radius

EAN: 4002516555056 / Material number: 12032360 / Old Material Number: 41GDF513GB

|  |                         |
|--|-------------------------|
| <b>Construction type</b>                   |                         |
| Cylinder vacuum cleaner with dustbag       | •                       |
| Product brand                              | Complete C3             |
| Motor type                                 | PowerLine               |
| Product type                               | SGDF5                   |
| Appliance Colour                           | Graphite grey           |
| <b>User convenience</b>                    |                         |
| Electronic suction power control           | +/- footswitches        |
| Illuminated power indicator                | •                       |
| Ergonomic carrying handle                  | •                       |
| Ergonomic handle                           | •                       |
| Silence system                             | •                       |
| Suction tube                               | Comfort telescopic tube |
| Park system for pauses during vacuuming    | •                       |
| Park system                                | on both sides           |
| Comfort cable rewind                       | •                       |
| <b>Efficiency and sustainability</b>       |                         |
| Nominal power consumption in W             | 890                     |
| <b>Mobility</b>                            |                         |
| Castors with steel shaft, gentle on floors | •                       |
| 3-point manoeuvrability                    | •                       |
| Operating radius in m                      | 12                      |
| Cable length in m                          | 8.5                     |
| <b>Filter system</b>                       |                         |
| Vacuum cleaner bag type                    | HyClean GN              |
| Dustbag volume in l                        | 4.5                     |
| Dustbag change indicator                   | •                       |
| Exhaust filter                             | AirClean filter         |
| Motor protection filter                    | •                       |
| <b>Safety</b>                              |                         |
| Locking system for floorhead and handle    | •                       |
| Automatic dustbag positioning              | •                       |
| All-round furniture protection strip       | •                       |
| <b>Technical data</b>                      |                         |
| Max. power                                 | 890                     |
| Volume in dB                               | 77.0                    |
| Width in mm                                | 496                     |
| Height in mm                               | 227                     |
| Weight in kg                               | 7.3                     |
| <b>Accessories included</b>                |                         |
| Three-piece accessory set                  | Integrated              |
| Upholstery nozzle                          | •                       |
| Crevice nozzle                             | •                       |
| Dusting brush with synthetic bristles      | •                       |
| SBD 365-3 floorhead                        | •                       |
| Filter                                     | AirClean filter         |
| Cleaning tool                              | No                      |