

KFN 4395 DD Freestanding fridge-freezer with DailyFresh, NoFrost and ComfortClean for great convenience.



- Spacious drawer with moisture control DailyFresh
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool
- Two separate air circuits for optimum cooling DuplexCool
- Dishwasher-safe door shelves ComfortClean



Appliance category Fridge-freezer Construction type Freestanding appliance Door hinge right Convertible door hinging Design Casing colour Silver Front colour Stainless look Refrigeration section lighting LED User convenience Freshness system DailyFresh ComfortClean DynaCool NoFrost • DuplexCool • XL interior VarioRoom Concealed door opener SideOpen Control system Operating concept SensorTouch Precise adjustment Fridge and freezer temperature Fridge compartment can be switched off Yes Independent temperature regulation of fridge and freezer Yes Automatic SuperCool SuperFreeze No. of temperature zones 2 Sabbath mode Party mode Holiday mode Fridge/Fridge section No. of shelves 5 No. of crisper drawers 1 Number of inner door racks for tinned food 3 Door rack for bottles 1 Door shelves 4 Freezer/Freezer section Number of freezer drawers 3 Efficiency and sustainability Energy efficiency class (A-G) Annual energy consumption in kWh 202.60 Energy consumption in 24 h in kWh 0.55 Safety Lock function Acoustic door alarm Acoustic temperature alarm Optical door alarm Optical temperature alarm

EAN: 4002516570301 / Material number: 12057030 / Old Material Number: 38439541GB



KFN 4395 DD Freestanding fridge-freezer with DailyFresh, NoFrost and ComfortClean for great convenience.



EAN: 4002516570301 / Material number: 12057030 / Old Material Number: 38439541GB


Power cut indication for freezer section	•
Technical data	
Appliance width in mm	600
Appliance height in mm	2015
Appliance depth in mm	675
Weight in kg	74.1
Climate class	SN-T
Refrigerator compartment in I	268
4* freezer compartment in I	103
Total usable capacity in I	371
Storage time in case of fault in h	20
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A-D)	С
Sound emissions in dB(A) re 1 pW	36
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.0
Replacing lamps	Service
Accessories included	
Egg tray	•
Ice cube tray	•

Miele

KFN 4395 DD


Freestanding fridge-freezer

with DailyFresh, NoFrost and ComfortClean for great convenience.




KFN4395DD, KFN4395CD, KFN4397CD, installation sketch (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.




Integrating freestanding refrigeration appliance in a run of kitchen units, edt/cs, ws, bst, el (*footnote)

1. Top box, 2. Refrigeration appliance, door depth = 75 mm , 3. Housing unit, 4. Wall, A = 25 mm (with recessed grip)/60 mm (with handle), * The appliance depth is increased by approx. 15 mm for refrigeration appliances with wall spacers fitted.



KFN4375DD, KFN4395DD, KFN4393FD, KFN4393D, KFN4377DD, KS4383ED, K4373ED, FN4312E, top view (footnote*)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4395DD, KFN4393FD, KFN4393DD, KFN4795DD bb, KFN4795CD bb, KFN4898CD, installation (footnote*)

 * 1. View from the front, 2. connection cable, L = 2000 mm

Mains