

KFN 4394 ED Freestanding fridge-freezer with DailyFresh ExtraCool, NoFrost and LED lighting for great convenience.



- 2 drawers, one with adjustable humidity DailyFresh ExtraCool
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool
- Handle-less design thanks to an integrated handle design
- More space and convenience thanks to XL interior cabinet



Appliance category Fridge-freezer Construction type Freestanding appliance Door hinge right Convertible door hinging Design Casing colour White Front colour White Refrigeration section lighting LED User convenience Freshness system DailyFresh DynaCool NoFrost • XL interior • VarioRoom Concealed door opener SideOpen Control system Operating concept EasyControl Precise adjustment Fridge and freezer temperature Yes Independent temperature regulation of fridge and freezer zones Automatic SuperCool SuperFreeze No. of temperature zones 2 Eco mode Fridge/Fridge section No. of shelves 5 Chrome-plated metal bottle rack No. of crisper drawers 2 Number of inner door racks for tinned food 3 Door rack for bottles 1 Door shelves 4 Freezer/Freezer section Number of freezer drawers 3 Efficiency and sustainability Energy efficiency class (A-G) 238.00 Annual energy consumption in kWh Energy consumption in 24 h in kWh 0.65 Safety Acoustic door alarm Acoustic temperature alarm Optical door alarm Optical temperature alarm Technical data 600 Appliance width in mm Appliance height in mm 2030 Appliance depth in mm 660

73.4

EAN: 4002516572220 / Material number: 12057060 / Old Material Number: 38439454GB

Weight in kg



KFN 4394 ED Freestanding fridge-freezer with DailyFresh ExtraCool, NoFrost and LED lighting for great convenience.



EAN: 4002516572220 / Material number: 12057060 / Old Material Number: 38439454GB

Climate class

SN-T


Climate class	SIV-I
Refrigerator compartment in I	279
4* freezer compartment in I	89
Total usable capacity in I	368
Storage time in case of fault in h	12
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A-D)	C
Sound emissions in dB(A) re 1 pW	39
Current consumption (mA)	1500
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.1
Replacing lamps	Service
Accessories included	
Egg tray	•
Ice cube tray	•

Míele


KFN 4394 ED


Freestanding fridge-freezer

with DailyFresh ExtraCool, NoFrost and LED lighting for great convenience.



KFN4374ED, KDN4074E Active, KDN4071E Active, KDN4174E Active, KFN4391ED, KFN4394ED, top view (installation drawings)





Integrating freestanding refrigeration appliance in a run of kitchen units, edt/cs, ws, bst, el (*footnote)

1. Top box, 2. Refrigeration appliance, door depth = 75 mm, 3. Housing unit, 4. Wall, A = 25 mm (with recessed grip)/60 mm (with handle), * The appliance depth is increased by approx. 15 mm for refrigeration appliances with wall spacers fitted.