


G 5740 SC SL

Freestanding dishwasher, 45 cm
for optimum drying results thanks to AutoOpen drying.



- Perfect results in less than one hour – QuickPowerWash
- Save up to 50 % more electricity – hot water connection
- Everything completely dry – AutoOpen drying
- Very easy door opening and closing – ComfortClose
- Versatile and secure – ExtraComfort basket design




EAN: 4002516610434 / Material number: 12153410 / Old Material Number: 21574016GB

Model	
Freestanding dishwasher	•
45 cm dishwasher	•
Design	
Control panel colour	Brilliant White
Control panel version	Straight fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
Multilingua	•
Convenience	
Door closing aid	ComfortClose
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Efficiency and sustainability	
Energy efficiency class (A–G)	C
Water consumption in the Automatic programme in l from	6.0
Water consumption of the ECO programme in litres per programme cycle	7.9
Electricity consumption in the ECO programme in kWh	0.55
Energy consumption of the ECO programme in kWh after 100 programme cycles	55
Consumption value in kWh in the ECO programme with hot water connection	0.29
Duration of ECO programme in minutes	210
Noise emission class	B
Noise emissions in dB(A)	44
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Recirculation Turbothermic drying	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
Gentle	•
ExtraQuiet 40 dB(A)	•
Appliance care	•
Dishwashing options	
Short	•
IntenseZone	•
Express	•

G 5740 SC SL

Freestanding dishwasher, 45 cm
for optimum drying results thanks to AutoOpen drying.




EAN: 4002516610434 / Material number: 12153410 / Old Material Number: 21574016GB

Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	MultiFlex tray 45
Basket design	ExtraComfort 45 cm
Number of place settings	9
Safety	
Waterproof system	•
Safety lock	•
Technical data	
Niche width minimal in mm	450
Niche width max in mm	450
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600
Appliance width in mm	448
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119.5
Net weight in kg	48.4
Total rated load in kW	2.00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in m	1.50
Length of water drain hose in m	1.50
Length of supply lead in m	1.80
Available display languages	
Available display languages via MultiLingua	deutsch, english, español, français, italiano, nederlands, português, türkçe
Accessories included	
1 x UltraTabs box (20 tabs)	•
Voucher for 1 x box of UltraTabs (20 tabs) or 9 boxes at a reduced price	•

G 5740 SC SL

Freestanding dishwasher, 45 cm
for optimum drying results thanks to AutoOpen drying.



G7000, free standing dishwasher, 45cm (installation drawing)