

KWT 4584 E  
 Freestanding wine storage unit  
 with a temperature zone, ActiveHumidity and door lock.



- Perfect regulation of humidity with ActiveHumidity
- Protect your favourite wines with an integrated door lock
- Clever networking opens up new possibilities – Miele@home
- Presented in perfect light – LED lighting



EAN: 4002516612438 / Material number: 12156930 / Old Material Number: 39458451EU1

|  |                  |
|--|------------------|
| <b>Appliance category</b>                                      |                  |
| Wine conditioning unit   | •                |
| <b>Construction type</b>                                       |                  |
| Freestanding appliance   | •                |
| Door hinge   | right            |
| Convertible door hinging                                       | •                |
| <b>Design</b>  |                  |
| Casing colour  | black            |
| Front colour   | Black            |
| Wine compartment lighting                                      | LED illumination |
| <b>User convenience</b>  |                  |
| Networking with Miele@home                                     | •                |
| Concealed door opener  | SideOpen         |
| Silence system   | •                |
| No. of wooden racks  | 5                |
| Material of wooden racks                                       | Metal            |
| Low-vibration storage  | •                |
| <b>Control system</b>  |                  |
| Operating concept  | SensorTouch      |
| Independent temperature regulation of fridge and freezer zones | No               |
| No. of temperature zones                                       | 1                |
| Min. temperature setting range in °C                           | 5                |
| Max. temperature setting range in °C                           | 20               |
| Sabbath mode   | •                |
| <b>Fridge/Fridge section</b>                                   |                  |
| Dry back wall  | grey             |
| ActiveHumidity   | •                |
| <b>Efficiency and sustainability</b>                           |                  |
| Energy efficiency class (A–G)                                  | E                |
| Annual energy consumption in kWh                               | 95.36            |
| Energy consumption in 24 h in kWh                              | 0.26             |
| <b>Safety</b>  |                  |
| Door lock  | •                |
| Acoustic door alarm  | •                |
| Optical temperature alarm                                      | •                |
| <b>Technical data</b>  |                  |
| Appliance width in mm  | 597              |
| Appliance height in mm   | 1884             |
| Appliance depth in mm  | 763              |
| Weight in kg   | 73.0             |
| Climate class  | SN-T             |
| Wine compartment in l  | 433              |
| Total usable capacity in l                                     | 434              |
| 0.75 l Bordeaux bottle capacity (no. of bottles)               | 229 bottles      |
| Acoustic airborne noise emission class (A–D)                   | C                |
| Sound emissions in dB(A) re 1 pW                               | 38               |
| Current consumption (mA)                                       | 1500             |
| Voltage in V   | 220-240          |
| Fuse rating in A   | 10               |


KWT 4584 E  
Freestanding wine storage unit  
with a temperature zone, ActiveHumidity and door lock.



EAN: 4002516612438 / Material number: 12156930 / Old Material Number: 39458451EU1


|                             |       |
|-----------------------------|-------|
| Number of phases            | 1     |
| Frequency in Hz             | 50-60 |
| Length of supply lead in m  | 2.0   |
| <b>Accessories included</b> |       |
| Active AirClean filter      | •     |
| White chalk pen             | •     |

KWT 4584 E  
 Freestanding wine storage unit  
 with a temperature zone, ActiveHumidity and door lock.




KWT4584E sw, Rioja, installation sketch (\*footnote)  
 (installation drawings)

\*Dimension with wall spacers



KWT4584E sw, Rioja, top view (installation drawings)



KWT4584E sw, Rioja, installation (footnote\*) (installation drawings)

\*1. View from the front, 2. Mains connection cable, L = 2200 mm