

DOS G 80/1 comfort  
Hose metering pump  
with fill level indicator for automatic dispensing of liquid cleaning agents.



- For canisters up to 214 mm tall (up to canister opening)
- Dispensing up to 55 Milliliter per minute
- Adjustable via the dishwasher controls
- Flexible cap (covers DIN 50 and 51 threads)

EAN: 4002516647980 / Material number: 12187290 / Old Material Number: 67747545D

<b>Product category</b>	
Fresh-water dishwashers	•
<b>Machine affiliation</b>	
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
<b>Product category</b>	
External dispensing system	•
<b>Product properties</b>	
Material	Plastic
Colour	Grey, White
Production rate in ml/60 s	55
Length of suction lance in mm	214
Length of dispensing hose to suction lance in mm	1800
Length of dispensing hose from machine to dispensing module in mm	2850
Length of mains connection cable to machine in mm	2800
Minimum width of canister opening in mm	31
Maximum width of canister opening in mm	60
<b>Standard electrical connection</b>	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	200-230
Frequency in Hz	50
Total rated load in kW	0.01
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	114
External dimensions, net width in mm	115
External dimensions, net depth in mm	139
External dimensions, gross height in mm	160
External dimensions, gross width in mm	198
External dimensions, gross depth in mm	478
Net weight in kg	1.70
Gross weight in kg	2.56