


APLW 630

Insert

for the optimum loading of air regulators.



- Suitable for the reprocessing of 4 air regulators with ESA
- With small-part basket with 4 colour-codable compartments
- With compressed air connection and compressed air indicator
- Connection via quick couplings (compatible w. Parker Rectus 25®)
- For use in APLW 152, APLW 107 baskets and the E 975/2 mobile unit

EAN: 4002516707905 / Material number: 12229980 /
Old Material Number: 69663000D

Product category	
Large-chamber washer-disinfectors, fire brigades and emergency services	•
Machine affiliation	
PLW 8615 [Safety]	•
PLW 8616 [Safety]	•
PLW 8617 [Safety]	•
PLW 7111 [Safety]	•
Product category	
Insert for air regulators	•
Area of application	
Reprocessing of breathing air regulators	•
Product properties	
Material	Stainless steel, Plastic
Colour	Black, Stainless Steel
Compressed air indicator	•
Capacity	
Air regulators [number]	4
Dimensions and weight	
External dimensions, gross height in mm	255
External dimensions, gross width in mm	265
External dimensions, gross depth in mm	560
Net weight in kg	5.55
Gross weight in kg	6.01