

APLW 636

Insert

for the optimum loading of compressed air unit carrier frames and bottles.

EAN: 4002516697404 / Material number: 12230220 / Old Material Number: 69663600D



- For reprocessing up to 4 compressed air unit carrier frames
- For reprocessing up to 4 compressed air bottles
- Mixed reprocessing possible
- Pressurisation possible via small reprocessing bottles
- Flexible loading options
- For use in A 500 mobile unit

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615 [Safety]	•
PLW 8616 [Safety]	•
PLW 8617 [Safety]	•
Product category	
Insert for compressed air unit carrier frames	•
Insert for compressed air bottles	•
Product properties	
Material	Stainless steel
Colour	Stainless Steel
Area of application	
Reprocessing of compressed air unit carrier frames	•
Reprocessing of compressed air bottles	•
Capacity	
Compressed air bottles [number]	4
Compressed air unit carrier frames with compressed air bottle [number]	2
Compressed air unit carrier frames [number]	4
Dimensions and weight	
External dimensions, gross height in mm	460
External dimensions, gross width in mm	620
External dimensions, gross depth in mm	780
Net weight in kg	13.56
Gross weight in kg	13.56