

## PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 180.00 l, load size 18 (8.0) lb (kg) kg–10.0 kg
- Unique, gentle fabric care – honeycomb drum
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi
- Tested for intensive use – unparalleled Miele quality

EAN: 4002516657088 / Material number: 12258460 / Old Material Number: 52910001GB

### Construction type and version

|                                       |                  |
|---------------------------------------|------------------|
| Construction type                     | Front loader     |
| Range                                 | Performance Plus |
| Front                                 | Stainless steel  |
| Fascia color                          | Stainless steel  |
| Load in kg                            | 10.0             |
| Load size with a load ratio of 1:22.5 | 18 (8.0) lb (kg) |
| Load size with a load ratio of 1:18   | 10.0             |
| Load ratio                            | 1:18             |
| Drum volume in l                      | 180.00           |
| Drying system                         | Exhaust air      |
| Door opening [Ø] in mm                | 440              |
| Door opening angle in degrees         | 180              |
| Door hinge                            | left             |
| Stainless steel honeycomb drum        | Yes              |

### Application

|   |   |
|---|---|
| Suitable for the hotel and catering industry          | • |
| Suitable for retirement and care homes                | • |
| Suitable for facility management                      | • |
| Suitable for laundrettes                              | • |
| Suitable for residential homes and apartments         | • |
| Suitable for dry cleaners                             | • |
| Suitable for commercial laundries                     | • |
| Suitable for small businesses                         | • |
| Suitable for fire brigades and rescue services        | • |
| Suitable for studs, riding schools and stables        | • |
| Suitable for universities, nurseries, and schools     | • |
| Suitable for hospitals                                | • |
| Suitable for camp sites                               | • |
| Suitable for sports clubs                             | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for doctors' and dentists' practices         | • |
| Suitable for the petrochemicals industry              | • |
| Suitable for the food-processing industry             | • |
| Suitable for amusement parks & holiday complexes      | • |
| Suitable for state/community care facilities          | • |

### Performance data

|  |      |
|--|------|
| Maximum evaporation capacity in l/hour | 7.40 |
| Specific energy consumption in kWh/kg  | 0.51 |
| Programme duration in min.             | 36   |

### Control system

|                              |                              |
|------------------------------|------------------------------|
| Control system               | M Touch Pro                  |
| Programmability              | programmable                 |
| User interface               | Residual moisture controlled |
| Max. delay start in h        | 24                           |
| Time left display            | •                            |
| Programme sequence indicator | •                            |
| Selectable display languages | •                            |

## PDR 910 [EL]

Professional vented dryer, electric heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516657088 / Material number: 12258460 / Old Material Number: 52910001GB

| Standard electrical connection                 |                    |
|--|--------------------|
| Heating type                                   | Electric           |
| Electrical connection                          | 3N AC 400V 50/60HZ |
| Electric heater rating in kW                   | 7.94               |
| Total connected load in kW                     | 8.20               |
| Fuse rating in A                               | 16                 |
| Dimensions and weight                          |                    |
| External dimensions, height in mm              | 1020               |
| External dimensions, width in mm               | 700                |
| External dimensions, depth in mm               | 763                |
| External dimensions, gross height in mm        | 1215               |
| External dimensions, gross width in mm         | 760                |
| External dimensions, gross depth in mm         | 820                |
| Net weight in kg                               | 72.0               |
| Gross weight in kg                             | 80                 |
| Maximum floor load in N/m <sup>2</sup>         | 853                |
| Emissions data                                 |                    |
| Emission sound pressure level in the workplace | 50 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h         | 3.90               |
| Features                                       |                    |
| Intelligent drum reversal                      | •                  |
| Axial airflow                                  | •                  |
| Large-surface filter                           | •                  |
| PerfectDry                                     | •                  |
| SoftLift drum ribs                             | •                  |
| Low temperature function                       | •                  |
| Communication slot                             | •                  |
| Drum lighting                                  | •                  |
| Programme selection via colour frame           | •                  |
| Machine-independent accessories                | •                  |
| Connection options                             |                    |
| Payment system (optional)                      | •                  |
| Optical interface for service access           | •                  |
| Peak load cut-out/energy management (optional) | •                  |
| WiFi tumble dryer                              | •                  |
| Connector Box                                  | •                  |
| LAN module (optional)                          | •                  |
| Capacities                                     |                    |
| Respirator masks [number]                      | 4                  |
| Overalls [number]                              | 1                  |
| Over jackets [number]                          | 2                  |
| Synthetic duvets [number]                      | 1                  |
| Synthetic pillows [number]                     | 2                  |
| Down duvets [number]                           | 1                  |
| Down pillows [number]                          | 2                  |
| Cloths, 22 g [number]                          | 182                |
| Cotton mops, 40 cm [number]                    | 42                 |
| Cotton mops, 50 cm [number]                    | 36                 |
| Microfibre mops, 40 cm [number]                | 66                 |
| Microfibre mops, 50 cm [number]                | 47                 |
| Summer horse blankets [number]                 | 2                  |
| Standards, test certificates and symbols       |                    |
| VDE  | •                  |

PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.