

## PDR 516 SL TOP [G GS]

Vented dryer, galvanised sides, gas heated  
in SlimLine design, with easy-to-use time control.



- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Simple operation – easy to clean large fluff filter

EAN: 4002516659808 / Material number: 12263140 / Old Material Number: 52516025GB

Construction type and version	
Construction type	SlimLine
Range	Professional
Front	Iron grey
Fascia color	Stainless steel
Load in kg	16.0
Load size with a load ratio of 1:25	12.0
Load size with a load ratio of 1:18	16.0
Load ratio	1:18
Drum volume in l	300.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Stainless steel drum	•
Stainless steel honeycomb drum	No
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Performance data	
Maximum evaporation capacity in l/hour	14.50
Specific energy consumption in kWh/kg	0.65
Programme duration in min.	27
Control system	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	time-controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Standard electrical connection	
Heating type	Gas
Electrical connection	1N AC 230V 50/60HZ
Gas heater rating in kW	18.00
Total connected load in kW	0.60
Fuse rating in A	10
Dimensions and weight of dryer	
External dimensions, height in mm	1800
External dimensions, width in mm	711
External dimensions, depth in mm	1089

## PDR 516 SL TOP [G GS]

Vented dryer, galvanised sides, gas heated  
in SlimLine design, with easy-to-use time control.



EAN: 4002516659808 / Material number: 12263140 / Old Material Number: 52516025GB

External dimensions, gross height in mm	1810
External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1180
Net weight in kg	149.7
Gross weight in kg	163
Maximum floor load in N/m <sup>2</sup>	1704
<b>Emissions data</b>	
Emission sound pressure level in the workplace	56 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.70
<b>Features</b>	
Intelligent drum reversal	•
Large-surface fluff filter	•
SoftLift drum ribs	•
Retractable plinth	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
DVGW gas	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•