

PDR 511 SL ROP HP [EL IGS]

Heat-pump dryers

in SlimLine design, with residual moisture control, 230 V.



- 60 % lower energy consumption than vented dryer*
- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow

* Heat pump dryers consume up to 60 % less energy than an electrically heated vented dryer.

EAN: 4002516659815 / Material number: 12263180 / Old Material Number: 52511002GB

Construction type and version	
Construction type	SlimLine
Range	Professional
Front	Iron grey
Fascia color	Stainless steel
Load in kg	11.0
Load size with a load ratio of 1:25	8.0
Load size with a load ratio of 1:18	11.0
Load ratio	1:18
Drum volume in l	200.00
Drying system	Heat pump
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Stainless steel drum	•
Stainless steel honeycomb drum	No
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Performance data	
Maximum evaporation capacity in l/hour	4.50
Specific energy consumption in kWh/kg	0.22
Programme duration in min.	59
Control system	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Standard electrical connection	
Heating type	Heat pump with CleanStream
Electrical connection	1N AC 230V 50HZ
Heater rating, heat pump in kW	6.40
Total connected load in kW	3.00
Fuse rating in A	16
Dimensions and weight of dryer	
External dimensions, height in mm	1800
External dimensions, width in mm	711
External dimensions, depth in mm	1075

PDR 511 SL ROP HP [EL IGS]

Heat-pump dryers

in SlimLine design, with residual moisture control, 230 V.



EAN: 4002516659815 / Material number: 12263180 / Old Material Number: 52511002GB

External dimensions, gross height in mm	1810
External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1180
Net weight in kg	192.7
Gross weight in kg	206
Maximum floor load in N/m ²	2052
Emissions data	
Emission sound pressure level in the workplace	55 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2.30
Features	
Intelligent drum reversal	•
Large-surface fluff filter	•
Two-stage filtration	•
PerfectDry	•
SoftLift drum ribs	•
Retractable plinth	•
Machine-independent accessories	•
Efficiency and sustainability	
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R450a
Refrigerant quantity in kg	1.35
Refrigerant global warming potential in kg CO ₂ e	605
Appliance global warming potential in kg CO ₂ e	877
Connection options	
Payment system (optional)	•
Optical interface for service access	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•