

K 7125 E  
Built-in refrigerator  
with LED lighting and SuperCool for more convenience.




- Optimum and maintenance-free LED lighting in compartment
- Food is chilled quickly thanks to Automatic SuperCool



EAN: 4002516664239 / Material number: 12269690 / Old Material Number: 36712505EU1


<b>Appliance category</b>	
Refrigerator	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Refrigeration section lighting	LED
<b>Control system</b>	
Operating concept	EasyControl
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
No. of temperature zones	1
Party mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	3
Number of inner door racks for tinned food	1
Door rack for bottles	1
Door shelves	2
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	E
Annual energy consumption in kWh	92.00
Energy consumption in 24 h in kWh	0.25
<b>Safety</b>	
Acoustic door alarm	•
<b>Technical data</b>	
Niche height in mm min.	874
Niche depth in mm	550
Appliance width in mm	541
Appliance height in mm	874
Appliance depth in mm	548
Weight in kg	30.6
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	19
Climate class	SN-ST
Refrigerator compartment in l	136
4* freezer compartment in l	0
Total usable capacity in l	136
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	35
Current consumption (mA)	700
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.3
<b>Accessories included</b>	
Egg tray	•

K 7125 E  
Built-in refrigerator  
with LED lighting and SuperCool for more convenience.



K7118D, K7128D, K7116E, K7126E, K7117D, K7127D, K7115E, K7125E, built-in (footnote\*) (installation drawings)

\*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.



K7118D, K7128D, K7116E, K7126E, K7117D, K7127D, K7115E, K7125E, side view (installation drawings)