

## PLW 8617 [Safety EL]

Washer-disinfector for the reprocessing of breathing apparatus

– electric heating, single door, 1150 mm wide



- Performance/cycle ?? breathing masks and ?? air regulators
- Alternative load: 4 compressed air bottles or 4 carrier frames
- Intuitive operation and programmable controls
- High-performance system and specific programmes
- Reliable results thanks to spray arm monitoring

EAN: 4002516669166 / Material number: 12278690 / Old Material Number: 62861709GB

<b>Construction type and version</b>	
Construction type	Freestanding, 1 glass vertical sliding door
Type of heating	Electricity
Front/back	Stainless Steel
Side panels	Stainless steel
Single/multiple installations	•
Loading with mobile units	•
Electric door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•
<b>Application</b>	
Suitable for fire brigades and rescue services	•
<b>Capacity</b>	
Breathing masks [number]	24
Compressed air bottles [number]	4
Compressed air unit carrier frames with compressed air bottle [number]	2
Compressed air unit carrier frames [number]	4
<b>Performance data</b>	
Circulation pump, Qmax in l/min	400
Additional circulation pump for load carrier – direct coupling, Qmax in l/min	600
Variable-speed pump	•
Wash cabinet usable capacity in l	351
Tested operating hours	15000
Service life in wash cycles	20000
<b>Control system</b>	
Control type	PST 20
Programme selection	Full-touch colour display
Programmability	programmable
Free programme positions [number]	170
Automatic programme restart	•
Time left display	•
Programme sequence display	•
Status display via chamber lighting	•
Selectable display languages	•
<b>Standard electrical connection</b>	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	18.00
Total rated load in kW	20.00
Fuse rating in A	32-35
<b>Water connection/drainage</b>	
Cold water [number]	2
Hot water [number]	1
DI water [number]	2
Required flow pressure in kPa	200-1000
Maximum water hardness (cold water/hot water) in mmol/l	0.71
Drain valve [DN]	50
Drain pump (optional)	•

## PLW 8617 [Safety EL]

Washer-disinfector for the reprocessing of breathing apparatus

– electric heating, single door, 1150 mm wide



EAN: 4002516669166 / Material number: 12278690 / Old Material Number: 62861709GB

<b>Compressed air connection</b>	
Compressed air connection, technical [number]	1
Required compressed air, technical, in kPa	600-800
<b>Drying unit</b>	
Drying unit heating type	Electricity
Air throughput in m <sup>3</sup> /h	250
Time setting in 1-minute increments	1-240
HEPA filter class	H13
HEPA filter filtration efficiency (DIN EN 1822) in %	99.95
Electric heater rating in kW	8.00
<b>Dimensions and weight</b>	
External dimensions, net height in mm	1670
External dimensions, net width in mm	1150
External dimensions, net depth in mm	990
External dimensions incl. plinth/floor tray and top-box panelling, height in mm	2495
External dimensions, gross height in mm	1960
External dimensions, gross width in mm	1250
External dimensions, gross depth in mm	1130
Wash cabinet, height in mm	675
Wash cabinet, width in mm	650
Wash cabinet, depth in mm	800
Rack height above floor in mm	850
Net weight in kg	381
Gross weight in kg	393
Maximum floor load in N/m <sup>2</sup>	8000
<b>Emissions data</b>	
Sound pressure LpA in cleaning and drying according to DIN EN ISO 11201	<65 dB(A) re 20 µPa
<b>Programmes</b>	
Breathing apparatus	•
Vario FB Special	•
Vario FB Special Plus	•
Vario FB Chem	•
Vario FB Chem Plus	•
Drying FB	•
<b>Features</b>	
2 integrated diaphragm dispenser pumps for liquid media	•
Additional integrated dispenser pumps	4
Steam condenser (optional)	•
Volume flow control	•
Spray arm monitoring	•
Conductivity monitoring	•
Interface for process documentation	•
Multi-component filter system	•
Micro-fine filter	•
Load carrier – direct coupling	•
Integrated hot air drying (optional)	•
Integrated printer for process documentation (optional)	•
Heater elements outside wash cabinet	•
Setting options for process chemicals (4 x 10 l)	•

## PLW 8617 [Safety EL]

Washer-disinfector for the reprocessing of breathing apparatus

– electric heating, single door, 1150 mm wide



EAN: 4002516669166 / Material number: 12278690 / Old Material Number: 62861709GB

Wash cabinet made from high-quality stainless steel  
(1.4404/316L)

•

Plinth, on wheels (optional)

•

Multi-coloured chamber lighting

•

Modular basket design

•

### Connection options

Ethernet interface

•

External dispensing modules

•

USB interface

•

Central dispensing

•

Peak-load negotiation/energy management

•

### Standards, test certificates and symbols

CE

•

VDE (electrical safety)

•

EN 61010-2-040

•

Machinery Directive 2006/42/EC

•