

PDR 511 SL COP HP [EL IGS]

Heat-pump dryers

in SlimLine design, with time control, for connection to payment systems, 400 V.



- Drum volume 200.00 l, load size 8.0 kg–11.0 kg
- 60 % less energy consumption than vented dryers*
- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow

* Heat pump dryers consume up to 60 % less energy than an electrically heated vented dryer.

EAN: 4002516681281 / Material number: 12295740 / Old Material Number: 52511011GB

Construction type and version

Construction type	SlimLine
Range	Performance
Front	Iron grey
Fascia color	Stainless steel
Load size with a load ratio of 1:25	8.0
Load size with a load ratio of 1:18	11.0
Drum volume in l	200.00
Drying system	Heat pump
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Stainless steel drum	•
Stainless steel honeycomb drum	No

Application

Suitable for laundrettes	•
--------------------------	---

Performance data

Maximum evaporation capacity in l/hour	4.50
Specific energy consumption in kWh/kg	0.22
Programme duration in min.	59

Control system

Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	time-controlled
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•

Standard electrical connection

Heating type	Heat pump with CleanStream
Electrical connection	3N AC 400V 50HZ
Heater rating, heat pump in kW	6.40
Total connected load in kW	3.00
Fuse rating in A	16

Dimensions and weight of dryer

External dimensions, height in mm	1800
External dimensions, width in mm	711
External dimensions, depth in mm	1075
External dimensions, gross height in mm	1810
External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1180
Net weight in kg	192.7
Gross weight in kg	213
Maximum floor load in N	2052

Emissions data

Emission sound pressure level in the workplace	55 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	5.00

PDR 511 SL COP HP [EL IGS]

Heat-pump dryers

in SlimLine design, with time control, for connection to payment systems, 400 V.



EAN: 4002516681281 / Material number: 12295740 / Old Material Number: 52511011GB

Features

Intelligent drum reversal

•

Large-surface fluff filter

•

SoftLift drum ribs

•

Retractable plinth

•

Communication slot

•

Machine-independent accessories

•

Efficiency and sustainability

Recycling rate in %

91

Contains fluorinated greenhouse gases

•

Hermetically sealed system

•

Coolant

R450a

Refrigerant quantity in kg

1.35

Refrigerant global warming potential in kg CO₂e

605

Appliance global warming potential in kg CO₂e

877

Connection options

Payment system (optional)

•

Optical interface for service access

•

Peak-load negotiation / energy management (optional)

•

WiFi

•

Connector Box

•

LAN module (optional)

•

Standards, test certificates and symbols

CE

•

VDE

•

VDE-EMC

•

Splash-proof safety rating IPX4

•

WEEE

•

UKCA

•

Complies with Machinery Directive 2006/42/EC

•