

KFN 4795 CD

Freestanding fridge-freezer

with DailyFresh, NoFrost, DynaCool and added convenience.



- Spacious drawer with moisture control – DailyFresh
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool
- Two separate air circuits for optimum cooling – DuplexCool
- Soft closing of the door with SoftClose



EAN: 4002516701118 / Material number: 12335890 / Old Material Number: 38479537EU1

Appliance category	
Fridge-freezer	•
Construction type	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Casing colour	Silver
Front colour	Blackboard edition
Refrigeration section lighting	LED
User convenience	
Networking with Miele@home	•
Freshness system	DailyFresh
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
XL interior	•
VarioRoom	•
SoftClose	•
Concealed door opener	Click2open
Control system	
Operating concept	SensorTouch
Precise adjustment	Fridge and freezer temperature
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	Yes
Automatic SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Sabbath mode	•
Party mode	•
Holiday mode	•
Fridge/Fridge section	
No. of shelves	5
including number of split shelves (FlexiBoard)	1
Chrome-plated metal bottle rack	•
No. of crisper drawers	1
Number of inner door racks for tinned food	3
Door rack for bottles	1
Door shelves	4
Freezer/Freezer section	
Number of freezer drawers	3
Efficiency and sustainability	
Energy efficiency class (A–G)	C
Annual energy consumption in kWh	162.00
Energy consumption in 24 h in kWh	0.46
Safety	
Lock function	•

KFN 4795 CD

Freestanding fridge-freezer


with DailyFresh, NoFrost, DynaCool and added convenience.



EAN: 4002516701118 / Material number: 12335890 / Old Material Number: 38479537EU1


Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
Technical data	
Appliance width in mm	597
Appliance height in mm	2015
Appliance depth in mm	682
Weight in kg	77.7
Climate class	SN-T
Refrigerator compartment in l	268
4* freezer compartment in l	103
Total usable capacity in l	371
Storage time in case of fault in h	20
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A-D)	B
Sound emissions in dB(A) re 1 pW	35
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.0
Replacing lamps	Service
Accessories included	
Egg tray	•
Ice cube tray	•

KFN 4795 CD Freestanding fridge-freezer with DailyFresh, NoFrost, DynaCool and added convenience.




KFN4898CD bs, KS4887DD edt/cs, top view (footnote*)
(installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.




KFN4395DD, KFN4393FD, KFN4393DD, KFN4795DD bb,
KFN4795CD bb, KFN4898CD, installation (footnote*)

*1. View from the front, 2. Mains connection cable, L = 2000 mm



KFN4898AD, KFN4898CD, KFN4795DD bb, KFN4795CD
bb, installation sketch (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4795CD bb, KS4783DD obsw/matt, KFN4898AD
grgr, KFN4799AD obsw/matt 125 Gala Edition, top view
(installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.