

KFN 4375 CD

Freestanding fridge-freezer

with DailyFresh, NoFrost and ComfortClean for great convenience.



- Spacious drawer with moisture control – DailyFresh
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool
- Two separate air circuits for optimum cooling – DuplexCool
- Dishwasher-safe door shelves – ComfortClean



EAN: 4002516701248 / Material number: 12336030 /

Old Material Number: 38437534EU1

Appliance category	
Fridge-freezer	•
Construction type	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Casing colour	White
Front colour	White
Refrigeration section lighting	LED
User convenience	
Freshness system	DailyFresh
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
XL interior	•
VarioRoom	•
Concealed door opener	SideOpen
Control system	
Operating concept	SensorTouch
Precise adjustment	Fridge and freezer temperature
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	Yes
SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Sabbath mode	•
Party mode	•
Holiday mode	•
Fridge/Fridge section	
No. of shelves	4
No. of crisper drawers	1
Number of inner door racks for tinned food	2
Door rack for bottles	1
Door shelves	3
Freezer/Freezer section	
Number of freezer drawers	3
Efficiency and sustainability	
Energy efficiency class (A–G)	C
Annual energy consumption in kWh	160.60
Energy consumption in 24 h in kWh	0.44
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•

KFN 4375 CD

Freestanding fridge-freezer

with DailyFresh, NoFrost and ComfortClean for great convenience.



EAN: 4002516701248 / Material number: 12336030 /

Old Material Number: 38437534EU1

Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•

Technical data	
----------------	--

Appliance width in mm	597
Appliance height in mm	1855
Appliance depth in mm	675
Weight in kg	72.2
Climate class	SN-T
Refrigerator compartment in l	227
4* freezer compartment in l	103
Total usable capacity in l	330
Storage time in case of fault in h	20
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A-D)	B
Sound emissions in dB(A) re 1 pW	35
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.0
Replacing lamps	Service


Accessories included	
----------------------	--

Egg tray	•
Ice cube tray	•

KFN 4375 CD


Freestanding fridge-freezer

with DailyFresh, NoFrost and ComfortClean for great convenience.




KFN4375DD, KFN4375DD C, KFN4375CD, KFN4377DD, KFN4377CD, installation sketch (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4271CD, KFN4375DD, KFN4395DD, KFN4393FD, KFN4393D, KFN4377DD, KS4383ED, K4373ED, FN4312E, top view (footnote*)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4271CD, KFN4375DD, KFN4375DD C, KFN4375CD, KFN4377DD, KFN4377CD, installation (footnote*) (installation drawings)

*1. View from the front, 2. Mains connection cable, L = 2200 mm