

KFN 7734 C Built-in fridge-freezer combination DynaCool, convenient LED lighting and NoFrost for optimum storage.



- Spacious drawer with moisture control – DailyFresh
- Optimum and maintenance-free LED lighting in compartment
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance DynaCool
- Dishwasher-proof door shelves ComfortClean



Appliance category Fridge-freezer Construction type Built-in appliance Integrated appliance Door hinge right Convertible door hinging Design Refrigeration section lighting LED User convenience Networking with Miele@home Freshness system DailyFresh ComfortClean DynaCool NoFrost • DuplexCool • ComfortSize VarioRoom SoftClose • Control system Operating concept SensorTouch Fridge compartment can be switched off Yes Independent temperature regulation of fridge and freezer Yes zones Automatic SuperCool SuperFreeze No. of temperature zones 2 Sabbath mode • Party mode Holiday mode Fridge/Fridge section No. of shelves 5 including number of split shelves (FlexiBoard) 1 No. of crisper drawers 1 Number of inner door racks for tinned food 2 Door rack for bottles 1 Door shelves 3 Freezer/Freezer section 3 Number of freezer drawers Efficiency and sustainability Energy efficiency class (A-G) С 145.27 Annual energy consumption in kWh 0.39 Energy consumption in 24 h in kWh Safety Lock function

EAN: 4002516701422 / Material number: 12336440 / Old Material Number: 38773403GB

Power cut indication for freezer section

Acoustic door alarm
Acoustic temperature alarm
Optical door alarm
Optical temperature alarm



KFN 7734 C Built-in fridge-freezer combination DynaCool, convenient LED lighting and NoFrost for optimum storage.



EAN: 4002516701422 / Material number: 12336440 / Old Material Number: 38773403GB


Technical data	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	546
Weight in kg	63.6
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	18
Max. door front weight – freezer, in kg	12
Climate class	SN-T
Refrigerator compartment in I	183
4* freezer compartment in I	70
Total usable capacity in I	253
Storage time in case of fault in h	9
Freezer capacity in kg/24 h	6.00
Acoustic airborne noise emission class (A-D)	В
Sound emissions in dB(A) re 1 pW	33
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.2
Replacing lamps	Service
Accessories included	
Egg tray	•
Ice cube tray	•

Míele

KFN 7734 C


Built-in fridge-freezer combination

DynaCool, convenient LED lighting and NoFrost for optimum storage.




KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774D, installation (footnote*) (installation drawings)

*1. View from the front, 2. Mains connection cable, L = 2100 mm, 3. Ventilation cutout min. 200 cm², 4. Ventilation, 5. No connections permitted in this area



KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774D, built-in (footnote*) (installation drawings)

*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.



KFNS7734D, KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774D, side view (installation drawings)