

KFN 7744 C

Built-in fridge-freezer, 178 cm niche height

PerfectFresh Pro, LED lighting and NoFrost for best possible storage.



- Professional storage – fresher for longer with PerfectFresh Pro
- Optimum and maintenance-free LED lighting in compartment
- Clever networking opens up new possibilities – Miele@home
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool



EAN: 4002516711704 / Material number: 12361990 /
Old Material Number: 38774430EU1

| | |
|--|------------------|
| General information | |
| Model identifier | KFN 7744 C |
| Manufacturer material number | 12361990 |
| EAN number | 4002516711704 |
| Marketing class | Gold |
| Appliance category | |
| Fridge-freezer | • |
| Construction type | |
| Built-in appliance | • |
| Integrated appliance | • |
| Door hinge | right |
| Convertible door hinging | • |
| User convenience | |
| Fridge zone lighting | LED |
| Networking with Miele@home | • |
| Freshness system | PerfectFresh Pro |
| ComfortClean | • |
| ComfortSize | • |
| DynaCool | • |
| Party mode | • |
| Holiday mode | • |
| NoFrost | • |
| DuplexCool | • |
| VarioRoom | • |
| SoftClose | • |
| Ice/Water dispenser with mains water connection | No |
| Control system | |
| Operating concept | SensorTouch |
| Fridge compartment can be switched off | Yes |
| Independent temperature regulation of fridge and freezer zones | Yes |
| SuperCool | • |
| SuperFreeze | • |
| No. of temperature zones | 3 |
| Sabbath mode | • |
| Fridge/Fridge section | |
| No. of shelves | 3 |
| including number of split shelves (FlexiBoard) | 1 |
| Chrome-plated metal bottle rack | • |
| No. of crisper drawers | 2 |
| Dry back wall | CleanSteel |
| Number of inner door racks for tinned food | 1 |
| Door rack for bottles | 1 |
| Door shelves | 2 |
| Freezer/Freezer section | |
| Number of freezer drawers | 3 |
| Efficiency and sustainability | |
| Energy efficiency class (A–G) | C |

KFN 7744 C

Built-in fridge-freezer, 178 cm niche height

PerfectFresh Pro, LED lighting and NoFrost for best possible storage.



EAN: 4002516711704 / Material number: 12361990 /


Old Material Number: 38774430EU1

| | |
|--|------------|
| Annual energy consumption in kWh | 165.71 |
| Energy consumption in 24 h in kWh | 0.45 |
| Safety | |
| Lock function | • |
| Acoustic door alarm | • |
| Acoustic temperature alarm | • |
| Optical door alarm | • |
| Optical temperature alarm | • |
| Power cut indication for freezer section | • |
| Technical data | |
| Niche width in mm min. | 560 |
| Niche width in mm max. | 570 |
| Niche height in mm min. | 1772 |
| Niche height in mm max. | 1788 |
| Niche depth in mm | 550 |
| Appliance width in mm | 559 |
| Appliance height in mm | 1770 |
| Appliance depth in mm | 546 |
| Weight in kg | 71.3 |
| Door hinge technology | Fixed door |
| Max. door front weight – refrigerator, in kg | 18 |
| Max. door front weight – freezer, in kg | 12 |
| Climate range | SN-ST |
| Refrigerator compartment in l | 174 |
| including PerfectFresh zone in l | 71 |
| 4* freezer compartment in l | 70 |
| Total usable capacity in l | 244 |
| Storage time in case of fault in h | 9 |
| Freezer capacity in kg/24 h | 6.00 |
| Acoustic airborne noise emission class (A–D) | B |
| Sound emissions in dB(A) re 1 pW | 33 |
| Current consumption (mA) | 1400 |
| Voltage in V | 220-240 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Frequency in Hz | 50-60 |
| Length of supply lead in m | 2.2 |
| Replacing lamps | Service |
| Accessories included | |
| Egg tray | • |
| Water filter | Nein |
| Ice cube tray | • |

KFN 7744 C

Built-in fridge-freezer, 178 cm niche height

PerfectFresh Pro, LED lighting and NoFrost for best possible storage.



KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774B, installation

1. View from the front, 2. Mains connection cable, L = 2200 mm, 3. Ventilation cut-out min. 200 cm², 4. Ventilation, 5. No connections permitted in this area

KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774B, built-in

*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 560 mm niche but the energy consumption will be slightly higher.

KFNS7734D, KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774B, side view