

## Duoflex HX1

### Cordless stick vacuum cleaners

high suction | automatic power adjustment | appliance conversion | Sunset yellow



- Lithium-ion battery: up to 55 minutes running time with a single charge\*
- As powerful as a conventional Miele vacuum cleaner\*\*
- Light and compact: 3.1 kg / 0.3 l dust container
- Intelligent electrobrush with automatic power adjustment
- 99.99 %\*\*\* dust retention capacity with Hygiene filter

\* Valid for power level 1 without connected electrobrush.

\*\* Cleaning performance compared with a Miele Complete C3 cylinder vacuum cleaner (SGEF3) with STB 305-3 turbobrush (dust pickup from carpet and hard floor with crevices, fibre pickup from carpet). In accordance with IEC 62885-2.

\*\*\* In accordance with IEC 62885-4

EAN: 4002516714699 / Material number: 12377930 / Old Material Number: 41QLL032GB

| Construction type                     |                          |
|---------------------------------------|--------------------------|
| Cordless stick vacuum cleaners        | •                        |
| Product brand                         | Duoflex HX1              |
| Motor type                            | Digital Efficiency Motor |
| Product type                          | SQLL0                    |
| Construction type and design          |                          |
| Colour                                | Sunset yellow            |
| Cleaning                              |                          |
| Vortex Technology                     | •                        |
| User convenience                      |                          |
| Electronic suction power control      | Buttons / 2 levels       |
| Wall bracket                          | Standard                 |
| Accessory storage                     | HX-AH 20                 |
| Filter system                         |                          |
| ComfortClean                          | •                        |
| Dustbag volume in l                   | 0.3                      |
| Technical data                        |                          |
| Battery type                          | Li-ion                   |
| Nominal battery capacity in mAh       | 2500                     |
| Volume in dB                          | 79.0                     |
| Width in mm                           | 260                      |
| Height in mm                          | 1250                     |
| Weight in kg                          | 3.1                      |
| Running time MIN-stage PowerUnit solo | 55                       |
| Cleaning area in m <sup>2</sup>       | 60                       |
| Recharging time in min.               | 210                      |
| Nominal rating in W                   | 160                      |
| Accessories included                  |                          |
| Cleaning tool                         | Integrated               |
| MultiFloor electrobrush HX-EB 20      | •                        |
| HX-DB dusting brush                   | •                        |
| HX-UN upholstery nozzle               | •                        |
| HX-CN crevice nozzle                  | •                        |