

## KM 7373 FL Induction hob with onset controls with flex cooking area for large cookware



- Quick selection via numerical keybank – ComfortSelect
- 4 cooking zones incl. 1 flex cooking area
- A width of 800 mm for surfacemounted or flush-fit installation
- Communication with the cooker hood – automatic Con@ctivity function

EAN: 4002516733089 / Material number: 12399730 / Old Material Number: 26737370GB

Heating type	
Heating type	Induction
Construction type	
Independent of cooker	•
Design	
Elegant glass ceramic surface	•
Flush	•
Ceramic surface colour	Black
Surface-mounted installation	•
Cooking zone details	
Number of cooking zones	4
Number of cooking areas	1
Maximum number of pans	4
PowerFlex cooking zones	·
No.	2
Туре	Flex cooking zone
Diameter in mm	Ø 110-210
Rating in W	2100
Booster in W	3000
1st cooking zone/cooking area	0000
Position	front left
Туре	Dual-circuit ring
Size in mm	Ø 110-220
Max. Booster power rating in W	3000
Max. rating in W	2300
2nd cooking zone/cooking area	2300
Position	rear left
Туре	Dual-circuit ring
Size in mm	Ø 90-160
	1850
Max. Booster power rating in W	1400
Max. rating in W 3rd cooking zone/cooking area	1400
Position	right
	right Flex cooking zone
Type Size in mm	210x400
Max. Booster power rating in W	3700
Max. rating in W User convenience	3000
Miele@home	
Operation via sensor controls	ComfortSelect
Automatic function Con@ctivity	
Pan and pan size recognition	•
Extended cooking zone	• 
Display colour	Yellow
Auto heat-up	•
Keeping warm	•
Stop & Go function	•
Recall function	•
Safety switch-off	•
Permanent pan recognition	•



## KM 7373 FL Induction hob with onset controls with flex cooking area for large cookware





EAN: 4002516733089 / Material number: 12399730 / Old Material Number: 26737370GB

Individual setting options (e.g. buzzers)	•
Minute minder	•
Efficiency and sustainability	
Residual heat utilisation	•
Power rating in off mode in W	0.5
Power rating in standby mode in W	1.0
Power rating in networked standby in W	2.0
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
Cleaning and care	
Easy to clean ceramic glass	•
Safety	
Safety switch-off	•
Lock function	•
System lock	•
Integrated cooling fan	•
Overheating protection	•
Residual heat indicator	•
Technical data	
Dimensions in mm (width)	800
Dimensions in mm (height)	53
Dimensions in mm (depth)	520
Cutout dimensions in mm (width) with surface-mounted installation	750
Cutout dimensions in mm (depth) with surface-mounted installation	490
Casing height incl. connection box in mm	53
Internal cutout dimensions in mm (width) with flush installation	780
Internal cutout dimensions in mm (depth) with flush installation	500
Weight in kg	11
External cutout dimensions in mm (width) with flush installation	804
External cutout dimensions in mm (depth) with flush installation	524
Total rated load in kW	7.30
Length of supply lead in m	1.4
Voltage in V	230
Frequency in Hz	50-60
Accessories included	
Mains cable	Yes



KM 7373 FL Induction hob with onset controls with flex cooking area for large cookware





KM7373FL, KM7372FL surface-mounted (Installation drawing)

1) front, 2) Mains connection box, The mains connection cable (L = 1440 mm) is enclosed loose

KM7373FL, KM7372FL flush (Installation drawing)

1) front, 2) Mains connection box, The mains connection cable (L = 1440 mm) is enclosed loosely, 3) Step milling natural stone worktop, 4) Wooden strip 12 mm (no supplied accessories)