

G 7650 SCVi AutoDos Fully integrated dishwashers with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier Miele@home
- Incredibly low sound emissions of just 42 dB(a) dB(A)
- Fresh water dishwashers from 6.0 I in the Automatic programme
- Versatile and secure ExtraComfort basket design



Model	
Fully integrated dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	Obsidian Black
Control panel version	Fully integrated fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	optical and acoustic
Display language selection	•
Efficiency and sustainability	
Energy efficiency class (A-G)	A
Water consumption in the Automatic programme in I from	6.0
Water consumption of the ECO programme in litres per	8.4
programme cycle	
Electricity consumption in the ECO programme in kWh	0.54
Energy consumption of the ECO programme in kWh after 100 programme cycles	54
Consumption value in kWh in the ECO programme with hot water connection	0.29
Duration of ECO programme in minutes	230
Noise emission class	В
Noise emissions in dB(A)	42
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Recirculation Turbothermic drying	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
Intensive 75 °C	•
PowerWash	•
Gentle	•
Hygiene	•
SolarSave	•
	-

EAN: 4002516738442 / Material number: 12423970 / Old Material Number: 21765062GB



G 7650 SCVi AutoDos Fully integrated dishwashers with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516738442 / Material number: 12423970 / Old Material Number: 21765062GB

ExtraQuiet 37 dB(A)	•
Appliance care	•
Dishwashing options	
AutoDos	<u> </u>
Express	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort
Number of place settings	14
MultiClip	•
Safety	
Waterproof system	•
Filter indicator light	•
Safety lock	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	550
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	550
Depth with door open in cm	116.5
Net weight in kg	48.0
Total rated load in kW	2.00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
	1.50
Length of water inlet hose in m	1.50
Length of water drain hose in m	1.80
Length of supply lead in m	
Min. front panel weight in kg	4.0
Max. front panel weight in kg	11.0
[can be retrofitted by Service to min.]	7.0
[can be retrofitted by Service to max.]	14.0
Available display languages	lankana verde eta eta eta eta eta eta eta eta eta et
Available display languages via MultiLingua	bahasa malaysia, deutsch, english (AU), english (GB),
Accessories included	,
1 x PowerDisk	<u>•</u>
Voucher for 6 x PowerDisk	•