

G 7980 SCVi AutoDos K2O  
Fully integrated dishwashers  
– the Miele all-rounder for handleless kitchen designs.



- Automatic dispensing – AutoDos with integrated PowerDisk
- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier – Miele@home
- Automatic door opening after two knocks – Knock2open
- Quick swipe operation – M Touch display



EAN: 4002516738473 / Material number: 12424010 / Old Material Number: 21798062GB

|   |                           |
|---|---------------------------|
| <b>Model</b>  |                           |
| Fully integrated dishwasher   | •                         |
| 60 cm dishwasher  | •                         |
| <b>Design</b>   |                           |
| Control panel colour  | CleanSteel/Obsidian black |
| Control panel version   | Fully integrated fascia   |
| Control type  | Programme selector button |
| Display   | M Touch Vi                |
| Display colour  | White                     |
| MultiLingua   | •                         |
| <b>Convenience</b>  |                           |
| Networking with Miele@home  | •                         |
| Automatic dispensing with PowerDisk                                       | •                         |
| Knock2open  | •                         |
| Door closing aid  | AutoClose                 |
| BrilliantLight  | •                         |
| Time left display   | •                         |
| Delay start up to 24 hours  | •                         |
| In-operation indicator light  | optical and acoustic      |
| Add an item option  | •                         |
| Display language selection  | •                         |
| <b>Efficiency and sustainability</b>                                      |                           |
| Energy efficiency class (A–G)   | A                         |
| Water consumption in the Automatic programme in l from                    | 6.0                       |
| Water consumption of the ECO programme in litres per programme cycle      | 8.4                       |
| Electricity consumption in the ECO programme in kWh                       | 0.54                      |
| Energy consumption of the ECO programme in kWh after 100 programme cycles | 54                        |
| Consumption value in kWh in the ECO programme with hot water connection   | 0.29                      |
| Duration of ECO programme in minutes                                      | 230                       |
| Noise emission class  | B                         |
| Noise emissions in dB(A)  | 41                        |
| EcoFeedback   | •                         |
| EcoPower Technology   | •                         |
| Proven hygiene  | •                         |
| Hot water connection  | •                         |
| Half load   | •                         |
| <b>Quality of results</b>   |                           |
| Fresh water dishwasher  | •                         |
| SensorDry   | •                         |
| Recirculation Turbothermic drying   | •                         |
| Active condensation drying  | •                         |
| BrilliantGlassCare  | •                         |
| <b>Wash programmes</b>  |                           |
| QuickPowerWash  | •                         |
| ECO   | •                         |
| Automatic   | •                         |
| Intensive 75 °C   | •                         |
| PowerWash   | •                         |

G 7980 SCVi AutoDos K2O  
Fully integrated dishwashers  
– the Miele all-rounder for handleless kitchen designs.



EAN: 4002516738473 / Material number: 12424010 / Old Material Number: 21798062GB

|   |                   |
|---|-------------------|
| Gentle                                  | •                 |
| Hygiene                                 | •                 |
| SolarSave                               | •                 |
| ExtraQuiet 37 dB(A)                     | •                 |
| Pasta/Paella                            | •                 |
| Tall items 65°C                         | •                 |
| Appliance care                          | •                 |
| <b>Dishwashing options</b>              |                   |
| AutoDos                                 | •                 |
| Express                                 | •                 |
| Extra Clean                             | •                 |
| Extra dry                               | •                 |
| <b>Basket design</b>                    |                   |
| Cutlery loading                         | 3D MultiFlex tray |
| FlexCare glass holder                   | 2                 |
| FlexCare cup rack                       | 1                 |
| Basket design                           | MaxiComfort       |
| Number of place settings                | 14                |
| MultiClip                               | •                 |
| <b>Safety</b>                           |                   |
| Waterproof system                       | •                 |
| Filter indicator light                  | •                 |
| Safety lock                             | •                 |
| <b>Technical data</b>                   |                   |
| Niche width minimal in mm               | 600               |
| Niche width max in mm                   | 600               |
| Niche height minimal in mm              | 805               |
| Niche height maximal in mm              | 870               |
| Niche depth in mm                       | 550               |
| Appliance width in mm                   | 598               |
| Appliance height in mm                  | 805               |
| Appliance depth in mm                   | 550               |
| Depth with door open in cm              | 116.5             |
| Net weight in kg                        | 48.0              |
| Total rated load in kW                  | 2.00              |
| Voltage in V                            | 230               |
| Fuse rating in A                        | 10                |
| Number of phases                        | 1                 |
| Electrical frequency standard           | 50                |
| Length of water inlet hose in m         | 1.50              |
| Length of water drain hose in m         | 1.50              |
| Length of supply lead in m              | 1.80              |
| Min. front panel weight in kg           | 4.0               |
| Max. front panel weight in kg           | 11.0              |
| [can be retrofitted by Service to min.] | 7.0               |
| [can be retrofitted by Service to max.] | 14.0              |
| Replacing lamps                         | Service           |

G 7980 SCVi AutoDos K2O  
Fully integrated dishwashers  
– the Miele all-rounder for handleless kitchen designs.



EAN: 4002516738473 / Material number: 12424010 / Old Material Number: 21798062GB

#### Available display languages

Available display languages via MultiLingua

bahasa malaysia, dansk,  
deutsch, english (AU),  
english (GB), english (US),  
español, français (FR),  
hrvatski, italiano, magyar,  
nederlands, norsk, polski,  
português, русский,  
română, slovenčina,  
slovenščina, srpski,  
suomi, svenska, türkçe,  
українська, čeština,  
ελληνικά,

#### Accessories included

1 x PowerDisk

Voucher for 6 x PowerDisk

- 
-

G 7980 SCVi AutoDos K20  
Fully integrated dishwashers  
– the Miele all-rounder for handleless kitchen designs.



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,  
3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),