


APLW 882

Retrofitting kit

potential-free contacts for activating external signal receivers for PLW 8636.



- 10 potential-free contacts (4 inputs and 6 outputs)
- For external pumps, valves, fans and ring line systems, for example
- Installed by Customer Service

EAN: 4002516744597 / Material number: 12426880 / Old Material Number: 69688200D

Product category	
Washer-disinfectors, laboratory	•
Cleaning machines for industrial parts cleaning	•
Machine affiliation	
PLW 8636 [IPC]	•
PLW 8636 [LAB / LAB MON]	•
Product category	
Conversion kit	•
Connection module with potential-free contacts	•
Dimensions and weight	
External dimensions, gross height in mm	74
External dimensions, gross width in mm	327
External dimensions, gross depth in mm	463
Net weight in kg	0.96
Gross weight in kg	1.33