

KFN 4898 A-10 D

Freestanding fridge-freezer

for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.



- Super efficient A-10 %: 10 % more economical than energy efficiency class A
- Fresh 5 x longer with active humidification – PerfectFresh Active
- Flexible use of freezer – Freeze&Cool
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- Handleless appliances are easy to open thanks to Click2open
- No icing up of food and no need to defrost thanks to NoFrost



EAN: 4002516780885 / Material number: 12521940 / Old Material Number: 38489802EU1

Appliance category	
Fridge-freezer	•
Construction type	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Casing colour	BlackSteel
Front colour	BlackSteel
Refrigeration section lighting	FlexiLight 2.0
Freezer compartment lighting	LED
Fan lighting	•
Freshness system lighting	•
User convenience	
Networking with Miele@home	•
Freshness system	PerfectFresh Active
Freeze & Cool	•
Active humidification in top drawer	•
Fine adjustment inner door	•
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
XL interior	•
VarioRoom	•
SoftClose	•
SelfClose	•
Concealed door opener	Click2open
Control system	
Operating concept	FreshTouch
Precise adjustment	Fridge and freezer temperature
Fridge compartment can be switched off	Yes
Freezer section, can be deactivated	•
Independent temperature regulation of fridge and freezer zones	Yes
Automatic SuperCool	•
SuperFreeze	•
No. of temperature zones	3
Sabbath mode	•
Party mode	•
Holiday mode	•
Fridge/Fridge section	
No. of shelves	4
including number of split shelves (FlexiBoard)	1
of which illuminated	2
Chrome-plated metal bottle rack	•
No. of crisper drawers	2
Number of inner door racks for tinned food	2
Door rack for bottles	1

KFN 4898 A-10 D

Freestanding fridge-freezer

for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.




EAN: 4002516780885 / Material number: 12521940 / Old Material Number: 38489802EU1

Door shelves	3
Freezer/Freezer section	
Number of freezer drawers	3
Efficiency and sustainability	
Energy efficiency class (A-G)	A
Annual energy consumption in kWh	104.39
Energy consumption in 24 h in kWh	0.28
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
Technical data	
Appliance width in mm	597
Appliance height in mm	2015
Appliance depth in mm	675
Weight in kg	102.5
Climate class	SN-T
Refrigerator compartment in l	259
including PerfectFresh zone in l	99
4* freezer compartment in l	103
Total usable capacity in l	362
Storage time in case of fault in h	24
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A-D)	A
Sound emissions in dB(A) re 1 pW	29
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.0
Replacing lamps	Service
Accessories included	
Egg tray	•
PerfectFresh organisation box	•
Ice cube tray	•

KFN 4898 A-10 D


Freestanding fridge-freezer

for lasting freshness and convenience with PerfectFresh Active and Freeze&Cool.




KFN4898AD bs, KFN4898CD bs, installation sketch (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4898CD bs, KS4887DD edt/cs, top view (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4395DD, KFN4393FD, KFN4393DD, KFN4795DD bb, KFN4795CD bb, KFN4898CD, installation (footnote*)

*1. View from the front, 2. Mains connection cable, L = 2000 mm