

DAH 4980 Sienna

Wall mounted cooker hood

with matt black glass panel as an elegant highlight and SmartControl White



- Lots of headroom – with front panel, 898 mm wide
- Networking with Con@ctivity and Miele@home
- Efficient filtration- 10-ply stainless-steel grease filter
- ECO motor with minimum sound emissions at high air throughput
- Perfect match – glass panel and canopy in the same colour

A++

EAN: 4002516802938 / Material number: 12545650 / Old Material Number: 28H4980MGB

Construction type	
Wall mounted cooker hood	•
Operating modes	
Type of air guide	Can be retrofitted
Active charcoal filter (order separately)	DKF 29 charcoal filter
Design	
Colour	Obsidian black matt
Edge extraction	•
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
SmartControl White	•
ON/OFF switch	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Silence package	•
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A++
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	28.2
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	D
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	1 x 3,2 W
Light intensity in Lx	260 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
Fan	
Dual-action fan	•
DC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	215
Air throughput in Level 2 (m ³ /h) according to EN 61591	315
Air throughput in Level 3 (m ³ /h) according to EN 61591	415
Air throughput in Booster level (m ³ /h) according to EN 61591	660
Air throughput in booster level 2 (m ³ /h)	875
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	38.0

DAH 4980 Sienna
Wall mounted cooker hood
with matt black glass panel as an elegant highlight and SmartControl White



EAN: 4002516802938 / Material number: 12545650 / Old Material Number: 28H4980MGB

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	45.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	50.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	61.0
Sound power in Booster level 2 (dB(A) re 1 pW) acc. to EN 60704-3	68.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	24.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	31.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	36.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	47.0
Sound pressure in Booster level 2 (dB(A) re 20 µPa) acc. to EN 60704-2-13	54.0
Recirculation	
Air throughput in Level 1 (m³/h) according to EN 61591	175
Air throughput in Level 2 (m³/h) according to EN 61591	275
Air throughput in Level 3 (m³/h) according to EN 61591	430
Air throughput in Booster level 1 (m³/h) according to EN 61591	625
Air throughput in Booster level 2 (m³/h) according to EN 61591	720
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	46.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	53.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	64.0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	73.0
Sound power in Booster level 2 (dB(A) re 1 pW) acc. to EN 60704-3	76.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	39.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	50.0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	59.0
Sound pressure in Booster level 2 (dB(A) re 20 µPa) acc. to EN 60704-2-13	62.0
Safety	
Safety switch-off	•
Single-ply safety glass (ESG)	•
Technical data	
Overall hood height for extraction mode and external in mm	830–1210
Overall hood height for recirculation and external in mm	420
Overall height for vented and external in in. (mm)	830
Canopy width in mm	898

DAH 4980 Sienna
 Wall mounted cooker hood
 with matt black glass panel as an elegant highlight and SmartControl White





EAN: 4002516802938 / Material number: 12545650 / Old Material Number: 28H4980MGB

Overall height for extraction mode and external mode cooker hoods in mm	1210
Canopy height in mm	420
Overall height for recirculation in in. (mm)	420
Canopy depth in mm	381
Overall height for recirculation mode cooker hoods in mm	420
Minimum height above electric hobs in mm	450
Net weight in kg	18.0
Length of supply lead in m	1.3
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0.22
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Nein

DAH 4980 Sienna

Wall mounted cooker hood

with matt black glass panel as an elegant highlight and SmartControl White



DAH4970, DAH4980 Installation drawings

1) Break-through if the mains connection is not made with a mains plug, but with a fixed connection., 2) Exhaust air opening \varnothing 200 mm, so that the exhaust air line can be moved in the wall. Exhaust air connection \varnothing 150 mm to the top or alternatively to the rear., 3) Air outlet for recirculated air. The distance to the ceiling or furniture mounted above the unit should be at least 300 mm.