

## KFN 7833 D

Built-in fridge-freezer combination  
with DailyFresh and NoFrost in 194 cm height for a lot of storage space.



- 17 % more volume in the fridge section – Built-In XL
- Spacious drawer with moisture control – DailyFresh
- Optimum and maintenance-free LED lighting in compartment
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool



EAN: 4002516840602 / Material number: 12665220 /  
Old Material Number: 38783300EU1

| <b>Construction type</b>                       |                         |
|--|-------------------------|
| Integrated appliance                           | •                       |
| Door hinge                                     | right                   |
| <b>Design</b>                                  |                         |
| Refrigeration section lighting                 | LED                     |
| <b>User convenience</b>                        |                         |
| Networking with Miele@home                     | •                       |
| Freshness system                               | DailyFresh              |
| <b>Control system</b>                          |                         |
| Operating concept                              | SensorTouch             |
| Fridge compartment can be switched off         | Yes                     |
| No. of temperature zones                       | 2                       |
| <b>Fridge/Fridge section</b>                   |                         |
| No. of shelves                                 | 5                       |
| including number of split shelves (FlexiBoard) | 1                       |
| No. of crisper drawers                         | 1                       |
| Number of inner door racks for tinned food     | 3                       |
| Door rack for bottles                          | 1                       |
| Door shelves                                   | 3                       |
| <b>Efficiency and sustainability</b>           |                         |
| Energy efficiency class (A–G)                  | D                       |
| Annual energy consumption in kWh               | 180.31                  |
| Energy consumption in 24 h in kWh              | 0.49                    |
| <b>Technical data</b>                          |                         |
| Niche width in mm min.                         | 560                     |
| Niche width in mm max.                         | 570                     |
| Niche height in mm min.                        | 1940                    |
| Niche height in mm max.                        | 1950                    |
| Niche depth in mm                              | 550                     |
| Appliance width in mm                          | 541                     |
| Appliance height in mm                         | 1938                    |
| Appliance depth in mm                          | 545                     |
| Weight in kg                                   | 61.6                    |
| Door hinge technology                          | Sliding door connection |
| Max. door front weight – refrigerator, in kg   | 18                      |
| Max. door front weight – freezer, in kg        | 12                      |
| Climate class                                  | SN-T                    |
| Refrigerator compartment in l                  | 215                     |
| 4* freezer compartment in l                    | 70                      |
| Total usable capacity in l                     | 284                     |
| Storage time in case of fault in h             | 9                       |
| Freezer capacity in kg/24 h                    | 6.00                    |
| Acoustic airborne noise emission class (A–D)   | B                       |
| Sound emissions in dB(A) re 1 pW               | 33                      |
| Current consumption (mA)                       | 1400                    |
| Voltage in V                                   | 220-240                 |
| Fuse rating in A                               | 10                      |
| Number of phases                               | 1                       |

KFN 7833 D

Built-in fridge-freezer combination

with DailyFresh and NoFrost in 194 cm height for a lot of storage space.




EAN: 4002516840602 / Material number: 12665220 /  
Old Material Number: 38783300EU1

|                             |         |
|-----------------------------|---------|
| Frequency in Hz             | 50-60   |
| Length of supply lead in m  | 2.2     |
| Replacing lamps             | Service |
| <b>Accessories included</b> |         |
| Egg tray                    | •       |
| Ice cube tray               | •       |


## KFN 7833 D

Built-in fridge-freezer combination with DailyFresh and NoFrost in 194 cm height for a lot of storage space.




KFN7833D, built-in (footnote\*) (drawings)

\*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.



KFN7833D, installation (footnote\*) (drawings)

\*1. View from the front, 2. Mains connection cable, L = 2100 mm, 3. Mains Ventilation cut-out min. 200 cm<sup>2</sup>, 4. Ventilation, 5. No connections permitted in this area



KFN7833D, side view (drawings)