

DU 1150

Drying unit, electric

For machines 1150 mm wide & optimum internal & external drying of wash items.



- With top-box panelling; air supply via the ceiling installation
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash chamber
- Air flow rate 250 m³/h
- HEPA filter service life: 1000 hours

EAN: 4002516854555 / Material number: 12678650 /
Old Material Number: 69250008D

Product category

Large-capacity washer-disinfectors, laboratory

•

Machine affiliation

PLW 8617

•

Product properties

Material

Stainless steel

Colour

Stainless Steel

Dimensions and weight

External dimensions, net height in mm

855

External dimensions, net width in mm

850

External dimensions, net depth in mm

1190

External dimensions, gross height in mm

1010

External dimensions, gross width in mm

850

External dimensions, gross depth in mm

1200

Net weight in kg

120.00

Gross weight in kg

137.00