

DU 900

Drying unit, electric

For machines 900 mm wide & optimum internal & external drying of wash items.



- With top-box panelling; air supply via the ceiling installation
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash chamber
- Air flow rate 250 m³/h
- HEPA filter service life: 1000 hours

EAN: 4002516854722 / Material number: 12678660 / Old Material Number: 69250009D

Product category

Large-capacity washer-disinfectors, laboratory

•

Machine affiliation

PLW 8615

•

PLW 8616

•

Dimensions and weight

External dimensions, net height in mm

845

External dimensions, net width in mm

845

External dimensions, net depth in mm

1045

External dimensions, gross height in mm

1000

External dimensions, gross width in mm

845

External dimensions, gross depth in mm

1200

Net weight in kg

115.00

Gross weight in kg

132.00