

KFN 7774 B

Built-in fridge-freezer combination

with PerfectFresh Active, DynaCool and NoFrost for optimum storage.



- Door shelf heights can be adjusted individually
- Fresh 5x longer with active humidification – PerfectFresh Active
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool



EAN: 4002516895312 / Material number: 12819470 /  
Old Material Number: 38777406EU1

<b>Appliance category</b>	
Fridge-freezer	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Freezer compartment lighting	LED
Fan lighting	•
Freshness system lighting	•
<b>User convenience</b>	
Fridge zone lighting	FlexiLight 2.0
Networking with Miele@home	•
Freshness system	PerfectFresh Active
Active humidification in top drawer	•
Fine adjustment inner door	•
ComfortClean	•
DynaCool	•
Party mode	•
Holiday mode	•
NoFrost	•
DuplexCool	•
ComfortSize	•
VarioRoom	•
SoftClose	•
SelfClose	•
<b>Control system</b>	
Operating concept	FreshTouch
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	Yes
SuperCool	•
SuperFreeze	•
No. of temperature zones	3
Sabbath mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	4
including number of split shelves (FlexiBoard)	1
of which illuminated	2
No. of crisper drawers	2
Dry back wall	CleanSteel
Number of inner door racks for tinned food	1
Door rack for bottles	1
Door shelves	2
<b>Freezer/Freezer section</b>	
Number of freezer drawers	3
of which on runners	2

KFN 7774 B

Built-in fridge-freezer combination  
with PerfectFresh Active, DynaCool and NoFrost for optimum storage.




EAN: 4002516895312 / Material number: 12819470 /  
Old Material Number: 38777406EU1

Efficiency and sustainability	
Energy efficiency class (A–G)	B
Annual energy consumption in kWh	131.77
Energy consumption in 24 h in kWh	0.36
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
Technical data	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	546
Weight in kg	73.6
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	18
Max. door front weight – freezer, in kg	12
Climate range	SN-T
Refrigerator compartment in l	175
including PerfectFresh zone in l	71
4* freezer compartment in l	70
Total usable capacity in l	245
Storage time in case of fault in h	9
Freezer capacity in kg/24 h	6.00
Acoustic airborne noise emission class (A–D)	A
Sound emissions in dB(A) re 1 pW	29
Current consumption (mA)	1400
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.2
Replacing lamps	Service
Accessories included	
Egg tray	•
PerfectFresh organisation box	•
Ice cube tray	•


## KFN 7774 B

Built-in fridge-freezer combination  
with PerfectFresh Active, DynaCool and NoFrost for optimum storage.




KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774B, installation

1. View from the front, 2. Mains connection cable, L = 2200 mm, 3. Ventilation cut-out min. 200 cm<sup>2</sup>, 4. Ventilation, 5. No connections permitted in this area



KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774B, built-in

\*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.



KFNS7734D, KFN7734C, KFN7734F, KFN7734D, KFN7764D, KFN7785D, KFN7744E, KFN7774B, side view